






FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 	product family CARD CONN		
ltr	ecn no	dr	date	tolerances unless otherwise specified					title		
J	V50963	LSS	08/15/95	angles linear		.XX	±.01/.3	INCH/MM ↔	SDT SURFACE MOUNT CARD CONNECTOR		
K	V70466	MDF	10/01/97			.XXX	±.005/.13				
L	V80029	LSS	01/30/96		0"±2"	.XXXX	±.020/.051				
M	V02386	AZ	10/06/00	dr	J. SHREINER	3/17/90			dwg no		
N	V20148	GIP	02/01/02	enfr	M. HAHN	3/17/90			sheet 1 of 7		
P	M05-0181	MHT	8/22/05	chr	M. HAHN	3/17/90			67848		
R	M06-0117	AEA	06/27/06	appd	M. HAHN	3/17/90			A3		
sheet		revision		R	R	R	R				
index		sheet		1	2	3	4	5	6	7	
				4				5		6	


form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



TAPE AND REEL PACKAGING ONLY
SEE NOTE 8

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN					
ltr	ecn	no	dr	date	tolerances unless otherwise specified							title				
R					angles		linear		INCH/MM 		SDT SURFACE MOUNT CARD CONNECTOR					
									scale 4:1							
					dr		J. SHREINER		3/17/90		dwg no		sheet 2 of 7		size	
					enrg		M. HAHN		3/17/90		67848				A3	
					chr		M. HAHN		3/17/90							
					appd		M. HAHN		3/17/90		FCI 		type		Product Customer Drawing	
sheet index		revision sheet		1												

form: A3

PRODUCT NUMBER
SEE TABLE




FIGURE 1
SCALE: 10:1
RECOMMENDED PCB FOOT PRINT
SEE NOTE 3

NOTES:

1. HOUSING MATERIAL: FILLED, HI TEMP NYLON, COLOR: BLACK
2. TERMINAL MATERIAL: BODY, .010/.25 THICK BRASS
SPRING, BeCu, HEAT TREATED
BODY PLATING: 30u"/.76um Au OVER 50u"/1.27um Ni IN CONTACT AREA.
SOLDERTAIL: 100u"/2.54um TIN/LEAD OVER 50u"/1.27um Ni
SPRING PLATING: Au FLASH
LF SOLDER TAIL:
100u"/2.54um Sn OVER 50u"/1.27um Ni. (NOTE 13)
3. APPLICATION INFORMATION:
A. RECOMMENDED SOLDER PAD PATTERN IS SHOWN IN FIG. 1.
B. ALL MATING PINS TO BE .025/.64 SQ.ON TRUE CENTER OF GIVEN TERMINAL SPACING WITHIN .015/.39 DIA.
C. SUGGESTED MATING PIN LENGTH .350±.020/8.89±0.51.
4. TERMINAL MATERIAL: BODY, .010/.25 THICK
SPRING, BeCu, HEAT TREATED.
BODY PLATING: 30u"/.76um Au OVER 50u"/1.27um Ni IN CONTACT AREA.
SOLDERTAIL: Au FLASH
SPRING PLATING: Au FLASH
5. TAPE & REEL PACKAGING PER GES-14-344.
6. PART NUMBERS WITH THE SUFFIX "P" ADDED TO DASH NUMBER ARE TAPE & REEL PACKAGED.
7. TAPE & REEL PACKAGING FOR 24mm WIDE TAPE AND BELOW HAVE PILOT HOLE ON BOTH SIDES OF TAPE.
8. TAPE & REEL PACKAGING 56mm TAPE WIDTH, WITH 16mm POCKET PITCH
9. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
10. THESE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
11. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN A WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
12. THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WISKER GROWTH IN ALL INTERCONNECT REQUIREMENTS

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN								
ltr ecn no dr date					tolerances unless otherwise specified							title							
R					angles		linear		INCH/MM 		SDT SURFACE MOUNT CARD CONNECTOR								
							.XX ±.01/.3												
							.XXX ±.005/.13												
					0°±2°		.XXXX ±.0020/.051		scale 4:1										
					dr J. SHREINER		3/17/90				dwg no sheet 3 of 7 size								
					enr M. HAHN		3/17/90				67848 A3								
					chr M. HAHN		3/17/90												
					appd M. HAHN		3/17/90												
sheet index		revision sheet		1															

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER SEE TABLE	N. OF POS.	DIM. A	DIM. B	INSULATION PLUG	PLATING	TAPE & REEL PACKAGING	LEAD FREE OPTION
67848-001	2X1	.00/.0	.120/3.05	NO			NOTES 10,11
-002	2X2	.10/2.5	.220/5.59	NO			
-003	2X3	.20/5.0	.320/8.13	NO	NOTE 5	NO	
-004	2X4	.30/7.6	.420/10.67	NO	NOTE 5	NO	
-005	2X5	.40/10.1	.520/13.21	NO	NOTE 2	NO	
-006	2X6	.50/12.7	.620/15.75	NO	NOTE 2	NO	
-007	2X7	.60/15.2	.720/18.27	NO	NOTE 2	NO	
-008	2X8	.70/17.7	.820/20.83	NO	NOTE 2	NO	
-009	2X9	.80/20.3	.920/23.37	NO	NOTE 2	NO	
-010	2X10	.90/22.8	1.020/25.91	NO	NOTE 2	NO	
-011	2X11	1.00/25.4	1.120/28.45	NO	NOTE 2	NO	
-012	2X12	1.10/27.9	1.220/30.99	NO	NOTE 2	NO	
-013	2X13	1.20/30.4	1.320/33.53	NO	NOTE 2	NO	
-014	2X14	1.30/33.0	1.420/36.07	NO	NOTE 2	NO	
-015	2X15	1.40/35.5	1.520/38.61	NO	NOTE 2	NO	
-016	2X16	1.50/38.1	1.620/41.15	NO	NOTE 2	NO	
-017	2X17	1.60/40.6	1.720/43.69	NO	NOTE 2	NO	
-018	2X18	1.70/43.1	1.820/46.23	NO	NOTE 2	NO	
-019	2X19	1.80/45.7	1.920/48.77	NO	NOTE 2	NO	
-020	2X20	1.90/48.2	2.020/51.31	NO	NOTE 2	NO	
-021	2X21	2.00/50.8	2.120/53.85	NO	NOTE 2	NO	
-022	2X22	2.10/53.3	2.220/56.39	NO	NOTE 2	NO	
-023	2X23	2.20/55.8	2.320/58.93	NO	NOTE 2	NO	
-024	2X24	2.30/58.4	2.420/61.47	NO	NOTE 2	NO	
-025	2X25	2.40/60.9	2.520/64.01	NO	NOTE 2	NO	
-026	2X26	2.50/63.5	2.620/66.55	NO	NOTE 2	NO	
-027	2X27	2.60/66.0	2.720/69.09	NO	NOTE 2	NO	
-028	2X28	2.70/68.5	2.820/71.63	NO	NOTE 2	NO	
-029	2X29	2.80/71.1	2.920/74.17	NO	NOTE 2	NO	
-030	2X30	2.90/73.6	3.020/76.71	NO	NOTE 2	NO	
-031	2X31	3.00/76.2	3.120/79.25	NO	NOTE 2	NO	
-032	2X32	3.10/78.7	3.220/81.79	NO	NOTE 2	NO	
-033	2X33	3.20/81.2	3.320/84.33	NO	NOTE 2	NO	
-034	2X34	3.30/83.8	3.420/86.87	NO	NOTE 2	NO	
-035	2X35	3.40/86.3	3.520/89.41	NO	NOTE 2	NO	
-036	2X36	3.50/88.9	3.620/91.95	NO	NOTE 2	NO	
-037	2X37	3.60/91.4	3.720/94.49	NO	NOTE 2	NO	
-038	2X38	3.70/93.9	3.820/97.03	NO	NOTE 2	NO	
-039	2X39	3.80/96.5	3.920/99.57	NO	NOTE 2	NO	
67848-040	2X40	3.90/99.0	4.020/102.11	NO	NOTE 2	NO	NOTES 10,11

UNASSIGNED
UNASSIGNED

mat'l. code				surface ISO 1302 ☒ / tolerance ISO 406 ISO 1101		projection 		product family CARD CONN			
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM		title			
R				angles	linear	.XX ±.01/.3 .XXX ±.005/.13 .XXXX ±.0020/.051		SDT SURFACE MOUNT CARD CONNECTOR			
				0'±2'		scale 4:1		dwg no sheet 4 of 7 size			
				dr	J. SHREINER	3/17/90		67848 A3			
				enr	M. HAHN	3/17/90					
				chr	M. HAHN	3/17/90					
				appd	M. HAHN	3/17/90					
sheet index	revision sheet	1									

form: A3



FCIconnect.com

Copyright FCI

form: A3

PRODUCT NUMBER	N. OF POS.	DIM. A	DIM. B	INSULATION PLUG	PLATING	TAPE & REEL PACKAGING	LEAD FREE OPTION
67848-041	2X41	4.00/101.6	4.120/104.65	NO	NOTE 2	NO	NOTES 10,11
-042	2X42	4.10/104.1	4.220/107.19	NO	NOTE 2	NO	
-043	2X43	4.20/106.6	4.320/109.73	NO	NOTE 2	NO	
-044	2X44	4.30/109.2	4.420/112.27	NO	NOTE 2	NO	
-045	2X45	4.40/111.7	4.520/114.81	NO	NOTE 2	NO	
-046	2X46	4.50/114.3	4.620/117.35	NO	NOTE 2	NO	
-047	2X47	4.60/116.8	4.720/119.89	NO	NOTE 2	NO	
-048	2X48	4.70/119.3	4.820/122.43	NO	NOTE 2	NO	
-049	2X49	4.80/121.9	4.920/124.97	NO	NOTE 2	NO	
-050	2X50	4.90/124.4	5.020/127.51	NO	NOTE 2	NO	
-051	2X51	5.00/127.0	5.120/130.05	NO	NOTE 2	NO	
-052	2X52	5.10/129.5	5.220/132.59	NO	NOTE 2	NO	
-053	2X53	5.20/132.0	5.320/135.15	NO	NOTE 2	NO	
-054	2X54	5.30/134.6	5.420/137.67	NO	NOTE 2	NO	
-055	2X55	5.40/137.1	5.520/140.21	NO	NOTE 2	NO	
-056	2X56	5.50/139.7	5.620/142.76	NO	NOTE 2	NO	
-057	2X57	5.60/142.2	5.720/145.29	NO	NOTE 2	NO	
-058	2X58	5.70/144.7	5.820/147.83	NO	NOTE 2	NO	
-059	2X59	5.80/147.3	5.920/150.37	NO	NOTE 2	NO	
-060	2X60	5.90/149.8	6.020/152.91	NO	NOTE 2	NO	
-061	2X61	6.00/152.4	6.120/155.45	NO	NOTE 2	NO	
-062	2X62	6.10/154.9	6.220/157.99	NO	NOTE 2	NO	
-063	2X63	6.20/157.4	6.320/160.53	NO	NOTE 2	NO	
-064	2X64	6.30/160.0	6.420/163.07	NO	NOTE 2	NO	
67848-065	2X65	6.40/162.5	6.520/165.61	NO	NOTE 2	NO	NOTES 10,11
67848-013P	2X13	1.20/30.4	1.320/33.53	NO	NOTE 2	YES	

NOTE 7 & 9

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family CARD CONN
ltr	ecn	no	dr	date	tolerances unless otherwise specified	 INCH/MM scale 4:1	title
R					angles linear .XX ±.01/.3 .XXX ±.005/.13 .XXXX ±.0020/.051		SDT SURFACE MOUNT CARD CONNECTOR
					0'±2'		
				dr	J. SHREINER 3/17/90		dwg no
				enr	M. HAHN 3/17/90		sheet5 of 7 size
				chr	M. HAHN 3/17/90		67848 A3
				appd	M. HAHN 3/17/90		type Product Customer Drawing
sheet index	revision sheet	1					



FCIconnect.com

Copyright FCI

1				2		3								4		5		6
PRODUCT NUMBER	N. OF POS.	DIM. A		DIM. B		INSULATION PLUG		PLATING		TAPE & REEL PACKAGING		LEAD FREE OPTION		UNASSIGNED				
67848-501	DISCONTINUED											NOTES 10,11						
-502	2X2	.10/2.5	.220/5.59	YES								UNASSIGNED						
-503	2X3	.20/5.0	.320/8.13	YES		NOTE 5		NO										
-504	2X4	.30/7.6	.420/10.67	YES		NOTE 5		NO										
-505	2X5	.40/10.1	.520/13.21	YES		NOTE 2		NO										
-506	2X6	.50/12.7	.620/15.75	YES		NOTE 2		NO										
-507	2X7	.60/15.2	.720/18.27	YES		NOTE 2		NO										
-508	2X8	.70/17.7	.820/20.83	YES		NOTE 2		NO										
-509	2X9	.80/20.3	.920/23.37	YES		NOTE 2		NO										
-510	2X10	.90/22.8	1.020/25.91	YES		NOTE 2		NO										
-511	2X11	1.00/25.4	1.120/28.45	YES		NOTE 2		NO										
-512	2X12	1.10/27.9	1.220/30.99	YES		NOTE 2		NO										
-513	2X13	1.20/30.4	1.320/33.53	YES		NOTE 2		NO										
-514	2X14	1.30/33.0	1.420/36.07	YES		NOTE 2		NO										
-515	2X15	1.40/35.5	1.520/38.61	YES		NOTE 2		NO										
-516	2X16	1.50/38.1	1.620/41.15	YES		NOTE 2		NO										
-517	2X17	1.60/40.6	1.720/43.69	YES		NOTE 2		NO										
-518	2X18	1.70/43.1	1.820/46.23	YES		NOTE 2		NO										
-519	2X19	1.80/45.7	1.920/48.77	YES		NOTE 2		NO										
-520	2X20	1.90/48.2	2.020/51.31	YES		NOTE 2		NO										
-521	2X21	2.00/50.8	2.120/53.85	YES		NOTE 2		NO										
-522	2X22	2.10/53.3	2.220/56.39	YES		NOTE 2		NO										
-523	2X23	2.20/55.8	2.320/58.93	YES		NOTE 2		NO										
-524	2X24	2.30/58.4	2.420/61.47	YES		NOTE 2		NO										
-525	2X25	2.40/60.9	2.520/64.01	YES		NOTE 2		NO										
-526	2X26	2.50/63.5	2.620/66.55	YES		NOTE 2		NO										
-527	2X27	2.60/66.0	2.720/69.09	YES		NOTE 2		NO										
-528	2X28	2.70/68.5	2.820/71.63	YES		NOTE 2		NO										
-529	2X29	2.80/71.1	2.920/74.17	YES		NOTE 2		NO										
-530	2X30	2.90/73.6	3.020/76.71	YES		NOTE 2		NO										
-531	2X31	3.00/76.2	3.120/79.25	YES		NOTE 2		NO										
-532	2X32	3.10/78.7	3.220/81.79	YES		NOTE 2		NO										
-533	2X33	3.20/81.2	3.320/84.33	YES		NOTE 2		NO										
-534	2X34	3.30/83.8	3.420/86.87	YES		NOTE 2		NO										
-535	2X35	3.40/86.3	3.520/89.41	YES		NOTE 2		NO										
-536	2X36	3.50/88.9	3.620/91.95	YES		NOTE 2		NO										
-537	2X37	3.60/91.4	3.720/94.49	YES		NOTE 2		NO										
-538	2X38	3.70/93.9	3.820/97.03	YES		NOTE 2		NO										
-539	2X39	3.80/96.5	3.920/99.57	YES		NOTE 2		NO										
67848-540	2X40	3.90/99.0	4.020/102.11	YES		NOTE 2		NO		NOTES 10,11								

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN			
ltr		ecn no		dr		date		tolerances unless otherwise specified		INCH/MM		title	
R								linear .XX ±.01/.3		scale 4:1		SDT SURFACE MOUNT CARD CONNECTOR	
								.XXX ±.005/.13				dwg no	
								.XXXX ±.0020/.051				sheet 6 of 7 size	
								dr J. SHREINER 3/17/90				A3	
								enr M. HAHN 3/17/90					
								chr M. HAHN 3/17/90					
								appd M. HAHN 3/17/90				type Product Customer Drawing	
sheet index		revision sheet		1									

form: A3



FCIconnect.com

Copyright FCI

form: A3

PRODUCT NUMBER		N. OF POS.	DIM. A	DIM. B	INSULATION PLUG	PLATING	TAPE & REEL PACKAGING	LEAD FREE OPTION										
67848-541	2X41	4.00/101.6	4.120/104.65	YES	NOTE 2	NO	NOTES 10,11											
-542	2X42	4.10/104.1	4.220/107.19	YES	NOTE 2	NO												
-543	2X43	4.20/106.6	4.320/109.73	YES	NOTE 2	NO												
-544	2X44	4.30/109.2	4.420/112.27	YES	NOTE 2	NO												
-545	2X45	4.40/111.7	4.520/114.81	YES	NOTE 2	NO												
-546	2X46	4.50/114.3	4.620/117.35	YES	NOTE 2	NO												
-547	2X47	4.60/116.8	4.720/119.89	YES	NOTE 2	NO												
-548	2X48	4.70/119.3	4.820/122.43	YES	NOTE 2	NO												
-549	2X49	4.80/121.9	4.920/124.97	YES	NOTE 2	NO												
-550	2X50	4.90/124.4	5.020/127.51	YES	NOTE 2	NO												
-551	2X51	5.00/127.0	5.120/130.05	YES	NOTE 2	NO												
-552	2X52	5.10/129.5	5.220/132.59	YES	NOTE 2	NO												
-553	2X53	5.20/132.0	5.320/135.15	YES	NOTE 2	NO												
-554	2X54	5.30/134.6	5.420/137.67	YES	NOTE 2	NO												
-555	2X55	5.40/137.1	5.520/140.21	YES	NOTE 2	NO												
-556	2X56	5.50/139.7	5.620/142.76	YES	NOTE 2	NO												
-557	2X57	5.60/142.2	5.720/145.29	YES	NOTE 2	NO												
-558	2X58	5.70/144.7	5.820/147.83	YES	NOTE 2	NO												
-559	2X59	5.80/147.3	5.920/150.37	YES	NOTE 2	NO												
-560	2X60	5.90/149.8	6.020/152.91	YES	NOTE 2	NO												
-561	2X61	6.00/152.4	6.120/155.45	YES	NOTE 2	NO												
-562	2X62	6.10/154.9	6.220/157.99	YES	NOTE 2	NO												
-563	2X63	6.20/157.4	6.320/160.53	YES	NOTE 2	NO												
-564	2X64	6.30/160.0	6.420/163.07	YES	NOTE 2	NO	NOTES 10,11											
67848-565	2X65	6.40/162.5	6.520/165.61	YES	NOTE 2	NO												

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN			
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title			
R					angles	linear	.XX ±.01/.3	INCH/MM	SDT SURFACE MOUNT				
							.XXX ±.005/.13		CARD CONNECTOR				
					0'±2'		.XXXX ±.0020/.051		scale 4:1				
					dr	J. SHREINER	3/17/90		dwg no		sheet 7 of 7		size
					enr	M. HAHN	3/17/90		67848				A3
					chr	M. HAHN	3/17/90						
					appd	M. HAHN	3/17/90		type		Product Customer Drawing		
sheet index		revision sheet		1									