


PRODUCT NO.
SEE TABLE



NOTES:

- MADE IN ACCORDANCE WITH PRODUCT SPEC. BUS-12-001.
- COLOR TO BE LIGHT BLUE WITH DARK BLUE TRACER ON EDGE OF FIRST POSITION ONLY
- UL LISTED STYLE 2651. CSA CERTIFIED PER C22.2 (LATEST REVISION).

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE				
ltr	ecn no	dr	date	tolerances unless otherwise specified						title				
A	—	TB	11/28/84	angles	linear	.XX±.01/.3				INCH/MM	#28 AWG SOLID DOUBLE SCALLOPED PVC RD. COND. CABLE			
B	V82043	RGD	11/13/98			.XXX±.005/.13								
C	M06-0282	MHT	7/26/06			.XXXX±.0020/.05								
				0'±2'		scale 1:1								
				dr	—	11/28/84				dwg no		sheet 1 of 2		size
				enrg	R.DOUTRICH	11/28/84				77060		A3		
				chr	R.DOUTRICH	11/28/84								
				appd	R.DOUTRICH	11/28/84								
sheet index		revision sheet		C	C									
				1	2									

PRODUCT NO.
77060-XXX

77060-XXX

NO. OF CONDUCTORS
(MIN. 9, MAX 64)
LENGTH

TOLERANCE FOR DIMS		
NO. OF CONDUCTORS	DIM. A±	DIM. B±
9 THRU 15	.007/-.18	.010/-.25
16 THRU 37	.009/-.23	.015/-.38
38 THRU 64	.011/-.28	.015/-.38

X	MIN. LENGTH FT/M
0	100/30.48
1	100/30.48
3	300/91.44
4	300/91.44

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE					
ltr	ecn	no	dr	date	tolerances unless otherwise specified					INCH/MM scale 1:1		title #28 AWG SOLID DOUBLE SCALLOPED PVC RD. COND. CABLE			
C					angles	linear	.XX±.01/.3	.XXX±.005/.13	.XXX±.0020/.051						
					0'±2'										
					dr		-	11/28/84			dwg no 77060 sheet 2 of 2 size A3				
					enr	R.DOUTRICH	11/28/84								
					chr	R.DOUTRICH	11/28/84								
					app	R.DOUTRICH	11/28/84								
sheet index		revision sheet													

form: A3