



343C2

Dual Input K-Type Thermocouple Thermometer with two GK13M Probes

343C1 consists of the following:

343 Thermometer



← A304 Boot
w/ tilt stand

- Auto Field Calibrate in less than 10 seconds in ice water to achieve +/- 1°F system (tester & probe) accuracy within 30°F to 120°F temperature range

Measurement Range (K-Type): -58 to 2,462 °F (-50 to 1,350 °C)

Resolution: 0.1° / 1°

Connector Type: Submini, Dual Input

GK13M K-Type Probe (x2)



Measurement Range: -165° to 400°F (-110° to 204°C)

Diameter: 28 gauge

Lead Length: 48" (1.2M)

Connector Type: Submini

Insulation Type: FEP