

LED Floating Lantern

EVEREADY®

5109L

WEATHERPROOF

- Meets IEC 60529 IPX4 requirements
- Survives rough weather on the job



FLOATS

- Floats for easy recovery from water



BRIGHT

- Provides 25 lumens
- Large reflector for broader beam



DURABLE

- Shatterproof lens
- Rugged polyethylene body
- Survives 1 meter drop



A great choice for wet areas and outdoor work, the 5109L is weatherproof and floats for easy recovery from water. It stays where you put it and provides a broad beam, making it a terrific area light. In addition, the light operates for 65 continuous hours using a 6V Carbon Zinc battery.

A shatterproof lens and a rugged polyethylene case help it stand up to rough job site conditions. Assembled in the USA using US and imported parts.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Eveready LED Floating Lantern
Model:	5109L
Color:	Yellow
Power Source:	One 6V Spring Terminal Lantern Battery
ANSI/NEDA:	Series 908D or 908A
Lamp:	Three White Nichia® LEDs
Lamp Life (hr):	Lifetime
Lamp Output (lumens):	25
Beam Distance (m):	82
Peak Beam Intensity (cd):	1,680
Run Time (h:mm):	65
Typical Weight:	230 grams (without battery)
Dimensions (mm):	112 x 185 x 99

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved