

BGA Heat Sink - High Performance ASIC Cooling



ATS Part#:	ATS-56000-C4-R0
Description:	30.00 x 30.00 x 9.00 mm BGA Heat Sink - High Performance ASIC Cooling
Heat Sink Type:	ASIC Cooling
Heat Sink Attachment:	Thermal Tape
Equivalent Part Number:	N/A

*Image above is for illustration purpose only.


Features & Benefits

- **maxiFLOW™** design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- Designed specifically for ASIC package and their unique cooling requirements

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	4 °C/W	3.3 °C/W	2.6 °C/W	2.3 °C/W	2 °C/W	1.8 °C/W	1.7 °C/W
	Ducted Flow	2.2	N/A	N/A	N/A	N/A	N/A	N/A

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	30.00 mm	30.00 mm	9.00 mm	44.6 mm	NO TIM	BLACK-ANODIZED
Notes: • Dimension A and B refer to component size. • Dimension C is the heat sink height from the bottom of the base to the top of the fin field. • Thermal performance data are provided for reference only. Actual performance may vary by application. • ATS reserves the right to update or change its products without notice to improve the design or performance. • ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant. • Contact ATS to learn about custom options available.						

*Image above is for illustration purpose only.

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA

