

Consolidated Electronic Wire & Cable

11044 King St

Franklin Park, IL 60131 US

Phone: 847-455-8830 • **Fax:** 847-455-8837**Toll-free:** 800-621-4278**Email:** info@conwire.com • **Website:** http://www.conwire.com**Part # 5176, 18 AWG (16 x 30) 2 Conductor Red and Black PVC Zip Automotive Speaker Cable****18 AWG (16 x 30) 2 Conductor Red and Black PVC Zip Automotive Speaker Cable****Product Construction****Conductors:**

- 18 AWG annealed stranded bare copper wire

Insulation:

- Red/Black Color coded flexible PVC
- Temperature: -20°C to +60°C
- Temperature: -20°C to +80°C (SAE J-1128)
- Voltage: 300 Volts
- Voltage: 60 Volts (SAE J-1128)

Applications:

- Stereo speaker wire
- Automotive speaker wire
- High definition low loss speaker cable
- Language lab

Industry Approvals:

- SAE J-1128
- OSHA acceptable
- RoHS Compliant

Packaging:

- 1000 ft. spools
- 500 ft. spools
- Also available on bulk reels

[· SPECIFICATIONS](#) · [OTHER INFORMATION](#) · [DISCLAIMER](#)**SPECIFICATIONS**

Conductor Size	18 AWG
Strands	16 x 30 Bare Copper Wire
No. of Conductors	2
Insulation Thickness	0.023 in.
Insulation Type	PVC
Nominal Diameter	0.092 x 0.190 in.
Color	Red/Black

Temperature	-20 to +60 / SAE J-1128 -20 to + 80 °C
Voltage	300 V

OTHER INFORMATION

Approvals	RoHS Compliant (2002/95/EC) SAE J1128
-----------	--

DISCLAIMER

Terms and Conditions for the Consolidated Electronic Wire and Cable Website Consolidated has made a very reasonable effort to ensure the accuracy of this “website” pertaining to the information, specifications and the “search” accuracy. The “website” is subject to errors and omissions. The content is subject to change without notice. This “website” is being constantly updated to correct any errors and omissions, but this does not ensure it is completely accurate. Drawings are for general reference only. Consolidated Electronic Wire &Cable is not liable for any direct, indirect, incidental or consequential damages resulting from the use of the material from this “website”.