




KWIK Wire Connector Blocks

Specification:-

Housing: High-temperature Resistant Thermoplastic 94-V2 grade
Metal Part: Plated Brass Insert

Voltage / Ampere : 450V/20A

Temperature : -20°C to 100°C (working) 130°C
(short-time)

Wiring Capacity : 0.5 - 2.5mm²

- Comply to IEC/EN 60998-1, 60998-2-2
- For use in junction boxes, power-houses and compact electrical devices
- Dovetail for stacking, with test-slot
- Push insertion and twist release




Tel :-

01933 234400

Fax :-

01933 234411



Web :- www.hylec-apl.com

Email :- sales@hylec-apl.com

Making The Right Connections