


VIDEO**GC™**

PHONO PIN PLUGS AND JACKS

Phono Pin Plug

**Specifications:****Pin:** RCA type. Nickel plated brass**Shell:** Cadmium plated brass**Handle:** Molded plastic or nickel plated brass**Terminals:** Combination clamp and solder type**Description:** Easier to attach than standard phono pin plug. Provides "finished" appearance

Metal

Cat. No. 33-0133-00BU


Black Plastic

Cat. No. 33-0131-00BU

Red Plastic

Cat. No. 33-0132-00BU

Phono Pin Jack

**Specifications:****Type:** RCA type. Cord mounting**Contacts:** Cadmium plated brass**Handle:** Molded plastic or nickel plated brass**Terminals:** Combination clamp and solder type**Description:** Also known as "extension" or "in-line" jack

Metal

Cat. No. 33-0134-00BU

N.S.N. 5935-00-023-5360

Single Hole Panel Phono Jack



2 Position Pushbutton Terminal Board



This terminal board mounts on most speaker cabinets, for easy wire connection. Red and black posts. Mounts in 2" hole, 1-1/4" deep, 1-3/4" mounting centers.

Cat. No. 33-1402-0000

4 Position Pushbutton Terminals



These terminals have spring loaded posts for easy connection with two red and two black. These are perfect for various audio applications, such as speaker connections, and amplifiers. 3" w x 1" h x 1-1/8" d, mounting centers 2-1/2".

Cat. No. 33-1404-0000

8 Position Pushbutton Terminals

These terminals have eight connecting posts, four red, and four black. The posts are spring loaded for easy connection. These terminals are designed for several audio applications, such as surround sound units, amplifiers, and speaker connections. 2-1/2" x 5/8" x 1-3/16", mounting centers 2-1/4".

Cat. No. 33-1408-0000

BNC Female to Dual Banana Plug

UPPER: BNC Female, gold plated center contact. Nickel plated brass body.**LOWER:** .750" Spaced dual banana plug. Brass body, beryllium copper nine piece leaf spring, nickel plated..

.164" Diameter holes in body for side stackable connection

Cat. No. 33-1191-0000**Cat. No. 33-1191-00BU****Banana Plugs**



5/64" Dia.

1/4" 32 Thd.

Specifications:**Body:** Nickel plated brass**Contacts:** Brass alloy**Insulator:** Phenolic**Washer:** Phenolic**Max. Panel Thickness:** 5/32"**Description:** Mounts in 9/32" hole**Cat. No. 33-0135-00BU****Banana Plugs**

With internal stud for solderless connection. Pkg. of one each red and black plastic handle.

Bulk Pack of Ten—Black

Cat. No. 33-0013-00BU

Bulk Pack of Ten—Red

Cat. No. 33-0015-00BU**VIDEO 13**