




DESCRIPTION: MALE - HIGH DENSITY - MACHINED CONTACTS - SOLDER CUP



ACCEPTS 28 - 24 AWG WIRE




MATERIAL:

- SHELL: STEEL MATERIAL, NICKEL FINISH
- INSULATOR: PBT THERMOPLASTIC 30% GLASS FILLED, UL 94V-0 RATED, BLACK
- CONTACT MATERIAL: BRASS
- CONTACT FINISH: SELECTIVE GOLD FINISHED
- SEALING MATERIAL: F08 FLEXIBLE ADHESIVE

ELECTRICAL:

- CONTACT CURRENT RATING: 5 AMPS
- CONTACT RESISTANCE: 30 Milliohms Max.
- DIELECTRIC WITHSTANDING VOLTAGE: 1,000VAC Min.
- INSULATION RESISTANCE: 5,000 Megohms Min.
- TEMPERATURE RATING: -55° ~ +105° C



DIMENSIONS (IN.)				
No. OF PINS	A	B	C	D
15	1.213	0.984	0.666	0.759
26	1.541	1.312	0.994	1.083
44	2.088	1.852	1.534	1.625

MEETS IP67 STANDARDS

(SEE PAGE 2 FOR SEALING DETAILS)

DO NOT SCALE FROM DRAWING

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

CHECKED:

DATE:
06-11-09

DATE:

NorComp

DWG NO.
780-MYY-103LYY1



SCALE:
1 : 1

SHEET
1

OF
2

REV
3


RoHS COMPLIANT



DETAIL A-A

HARDWARE OPTION

01X 0.065" (BOARD SIDE) - CN1



DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-26-09		
		CHECKED:		DATE:		
		SCALE: 2.5 : 1		SHEET OF 2 2		REV 3
		DWG NO. 780-MYY-103LYY1				