

## Single-Phase Basic PDU, 1.8kW 15A 120V, 0U Vertical Rackmount, 14 NEMA 5-15R outlets, NEMA 5-15P input plug

MODEL NUMBER: PDUV15



### Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

### Features

- PDUV15 offers highly reliable 15A 120V power distribution in a 36 in. / .9m 0U vertical rackmount format
- 14 NEMA 5-15R output receptacles
- NEMA 5-15P input plug
- 15 ft. / 4.6m attached line cord
- 15A resettable circuit breaker
- Switch-free design prevents accidental shutoff
- Toolless mounting buttons enable simple installation in Tripp Lite and other button-mount compatible equipment racks
- Rear facing installation buttons can be relocated to the left or right surface of the PDU for rear, center or forward-facing outlet orientation in compatible racks
- Included nut and bolt mounting brackets support installation in non button-mount compatible racks, wallmount and raceway applications

### Specifications

General Info	
Product Group	PDUS
OVERVIEW	

### Highlights

- 15A 120V Basic Power Distribution Unit
- 0U Vertical Rackmount format with 36 in / .9m height
- 14 NEMA 5-15R outlets
- NEMA 5-15P input plug
- 15 ft. / 4.6m attached line cord
- Toolless mounting buttons and bolt-down brackets included

### Applications

- Ideal for network power distribution in datacenters, computer rooms and network closets

### Package Includes

- PDUV15 Basic Vertical PDU
- Mounting hardware
- Owner's manual with warranty information

PDU Type	Basic
<b>OUTPUT</b>	
Output Capacity Details	Single-Phase Basic PDU, 1.8kW 15A 120V, 0U Vertical Rackmount, 14 NEMA 5-15R outlets, NEMA 5-15P input plug
Frequency Compatibility	50 / 60 Hz
Output (VA)	1800
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	15A
Outlet Quantity / Type	14 NEMA 5-15R
Outlet Type	NEMA 5-15R
<b>INPUT</b>	
PDU Input Voltage	100; 120; 127
Maximum Input Amps	15
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Phase	Single-Phase
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	40 x 2.8 x 3
Shipping Dimensions (hwd / cm)	101.6 x 7.11 x 7.62
Shipping Weight (lbs.)	3.8
Shipping Weight (kg)	1.72
Unit Dimensions (hwd / in.)	36 x 1.25 x 1.75
Unit Dimensions (hwd / cm)	91.44 x 3.18 x 4.45
Unit Weight (lbs.)	3.3
Unit Weight (kg)	1.50
Material of Construction	Aluminum
Style	Vertical Rackmount, Wallmount, Raceway, Workbench
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
PDU Form Factor	Vertical (0U)
<b>SPECIAL FEATURES</b>	
Appearance	Black housing

#### CERTIFICATIONS

Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
----------------	---

#### WARRANTY

Product Warranty Period (Worldwide)	5-year limited warranty
-------------------------------------	-------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.