

ESHF-125-01-L-D-SM-LC

ESHF-105-01-L-D-SM

EHF-125-01-L-D-SM-LC

SHF, ESHF, EHF, ECF SERIES

SHROUDED & EJECTOR IDC HEADER

FFSD*, FFTP

EHF — **1** **NO. PINS PER ROW** — **01** — **PLATING OPTION** — **D** — **TAIL OPTION** — **TAIL OPTION** — **OTHER OPTION**

04, 05, 08, 10, 13, 17, 20, 25
(Standard sizes)

—F
= Gold flash on post,
Matte Tin on tail

—L
= 10μ" (0.25 μm)
Gold on post,
Matte Tin on tail

Leave blank for Through-Hole version

—SM
= Surface Mount

—RA
= Right Angle

—“XX”
= Polarized Position
(—RA not available)

—LC
= Locking Clip
(—SM only)
(Manual placement required)

—K
= (7,50 mm) .295" DIA
Polyimide Film Pick
& Place Pad

—P
= Pick & Place Pad
(—SM only)

—TR
= Tape & Reel
Packaging
(—LC not available)

The diagram illustrates a 10-pin connector with various options. The top view shows a 10-pin configuration with dimensions: (1,27) .050 for pin pitch, (14,48) .570 for body length, and (0,41) .016 SQ for pin diameter. The side view shows a height of (11,30) .445. The detail view shows a pin diameter of (0,41) .016 SQ and a body diameter of (1,52) .060. The drawing includes plating options (—F, —L), tail options (—SM, —RA, —TH), and other options (—XX, —LC, —K, —P, —TR).

Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.