


# LAMINATED TRANSFORMERS

## Type EI30 / 18.0 - 2.3VA







- ⊕ Frequency 50/60Hz
- ⊕ Potted under vacuum
- ⊕ Split-bobbin
- ⊕ Temperature class ta 70°C/B
- ⊕ VDE rated as inherently short-circuit proof
- ⊕ Weight: 0.112kg
- ⊕ Packaging unit: 25 pieces (tube)

### Mechanical



### Schematics



| Primary (V) | Secondary (V / mA) | No-Load Voltage (V) | Schematic No. | Part Number | Agency Approvals |
|-------------|--------------------|---------------------|---------------|-------------|------------------|
| 230         | 6 / 384            | 10.00               | 1             | 030-7340.0  | 1/3*             |
| 230         | 9 / 256            | 13.80               | 1             | 030-7341.0  | 1/3*             |
| 230         | 12 / 192           | 18.60               | 1             | 030-7342.0  | 1/3*             |
| 230         | 15 / 154           | 23.80               | 1             | 030-7343.0  | 1/3*             |
| 230         | 18 / 128           | 27.80               | 1             | 030-7344.0  | 1/3*             |
| 230         | 24 / 96            | 34.70               | 1             | 030-7345.0  | 1/3*             |
| 230         | 2x6 / 192          | 2x9.90              | 2             | 030-7346.0  | 1/3*             |
| 230         | 2x9 / 128          | 2x14.00             | 2             | 030-7347.0  | 1/3*             |
| 230         | 2x12 / 96          | 2x17.50             | 2             | 030-7348.0  | 1/3*             |
| 230         | 2x15 / 77          | 2x24.40             | 2             | 030-7349.0  | 1/3*             |
| 230         | 2x18 / 64          | 2x29.30             | 2             | 030-7350.0  | 1                |
| 230         | 2x24 / 48          | 2x35.80             | 2             | 030-7351.0  | 1                |
| 115         | 6 / 384            | 10.00               | 1             | 030-7328.0  | 1/3*             |
| 115         | 9 / 256            | 13.80               | 1             | 030-7329.0  | 1/3*             |
| 115         | 12 / 192           | 18.60               | 1             | 030-7330.0  | 1/3*             |
| 115         | 15 / 154           | 23.80               | 1             | 030-7331.0  | 1/3*             |
| 115         | 18 / 128           | 27.80               | 1             | 030-7332.0  | 1/3*             |
| 115         | 24 / 96            | 34.70               | 1             | 030-7333.0  | 1/3*             |
| 115         | 2x6 / 192          | 2x9.90              | 2             | 030-7334.0  | 1/3*             |
| 115         | 2x9 / 128          | 2x14.00             | 2             | 030-7335.0  | 1/3*             |
| 115         | 2x12 / 96          | 2x17.50             | 2             | 030-7336.0  | 1/3*             |
| 115         | 2x15 / 77          | 2x24.40             | 2             | 030-7337.0  | 1/3*             |
| 115         | 2x18 / 64          | 2x29.30             | 2             | 030-7338.0  | 1                |
| 115         | 2x24 / 48          | 2x35.80             | 2             | 030-7339.0  | 1                |
| 2x115       | 6 / 384            | 10.00               | 3             | 030-6797.0  | 1/3*             |
| 2x115       | 9 / 256            | 13.80               | 3             | 030-6800.0  | 1/3*             |
| 2x115       | 12 / 192           | 18.60               | 3             | 030-6803.0  | 1/3*             |
| 2x115       | 15 / 154           | 23.80               | 3             | 030-6806.0  | 1/3*             |
| 2x115       | 18 / 128           | 27.80               | 3             | 030-6809.0  | 1/3*             |
| 2x115       | 24 / 96            | 34.70               | 3             | 030-6815.0  | 1/3*             |
| 2x115       | 2x6 / 192          | 2x9.90              | 4             | 030-6820.0  | 1/3*             |
| 2x115       | 2x9 / 128          | 2x14.00             | 4             | 030-6823.0  | 1/3*             |
| 2x115       | 2x12 / 96          | 2x17.50             | 4             | 030-6826.0  | 1/3*             |
| 2x115       | 2x15 / 77          | 2x24.40             | 4             | 030-6829.0  | 1/3*             |
| 2x115       | 2x18 / 64          | 2x29.30             | 4             | 030-6832.0  | 1                |
| 2x115       | 2x24 / 48          | 2x35.80             | 4             | 030-6838.0  | 1                |

\*NOTE: When checking the approval status of this product with VDE, add the prefix "BV" and the suffix "T" to the orderable Part Number (these letters will also be found on the part label). The prefix and suffix are not part of the orderable Part Number.