

Duplex Multimode 62.5/125 Fiber Patch Cable (ST/ST), 2M (6-ft.)

MODEL NUMBER: **N302-006**



Description

Tripp Lite's 6-ft. multimode duplex fiber optic ST/ST patch cable is manufactured from 62.5/125 zipcord fiber. The cable has ST connectors on each end, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 6-ft. Connectors: 2 ST connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Duplex multimode fiber is most commonly used in LAN applications where links are typically 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

OVERVIEW	
Fiber Type	62.5/125 - OM1
Intended Application	Computer Networking (Fiber)
Cable Type	MULTIMODE 62.5/125 FIBER OPTIC
Network Speed	1Gbps

Highlights

- Premium PVC 62.5/125 μ m multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Loop-back cables provide an easier, "single-person" solution for testing fiber optic cable systems

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with ST/ST connectors

Package Includes

- 6-ft. Duplex MMF Cable ST/ST 62.5/125 Fiber

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83
UPC ASSIGNMENT	
Unit Carton UPC#	037332013224
PHYSICAL	
Color	Orange
Style	Fiber Optic
CONNECTIONS	
Connector A	 ST
Connector B	 ST
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

Related Items

Optional Products

Model Number	Description	Qty.
N302-003	1M (3-ft.) Duplex MMF 62.5/125 Patch Cable (ST/ST)	1
N302-010	3M (10-ft.) Duplex MMF 62.5/125 Patch Cable (ST/ST)	1
N304-006	2M (6-ft.) Duplex MMF 62.5/125 Patch Cable (SC/ST)	1
N306-006	2M (6-ft.) Duplex MMF 62.5/125 Patch Cable (SC/SC)	1
N308-006	2M (6-ft.) Duplex MMF 62.5/125 Patch Cable (MTRJ/ST)	1
N310-006	2M (6-ft.) Duplex MMF 62.5/125 Patch Cable (MTRJ/SC)	1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

N314-02M	2M (6-ft.) Duplex MMF 62.5/125 Patch Cable (MTRJ/LC)	1
N316-02M	2M (6-ft.) Duplex MMF 62.5/125 Patch Cable (LC/SC)	1
N318-02M	2M (6-ft.) Duplex MMF 62.5/125 Patch Cable (LC/ST)	1
N320-02M	2M (6-ft.) Duplex MMF 62.5/125 Patch Cable (LC/LC)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:
<http://www.tripplite.com/sku/N302-006>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.