



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Heavy-Duty Power Extension Cord, 15A, 14AWG (IEC-320-C14 to IEC-320-C13), 6-ft.

MODEL NUMBER: P005-006



Highlights

- C13 to C14 Power Cable, 6 ft.
- 14 AWG x 3C
- 15A / 100 - 250V
- RoHS Compliant
- UL Listed

Package Includes

C13 to C14 Power Cable, 6 ft.

Description

Use Tripp Lite's P005-006 in server applications that require a higher rated, heavier gauge cable. C13 to C14 connectors, 3 x 14 AWG conductors, 15A rating, 100-250V.

Features

- Molded, Heavy-Duty Power Cable, 6 ft.
- IEC-60320-C13 to IEC-60320-C14
- 14 AWG x 3C, SJT, 15A, 100-250 Volt
- RoHS Compliant
- UL Listed

Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Shipping Dimensions (hwd / in.)	10.00 x 7.1 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Weight (lbs.)	0.71
Shipping Weight (kg)	0.32
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

ENVIRONMENTAL	
Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>