

6.00266.00 W 8-125 Quick

800 Watt Angle Grinder W 8-125 Quick



- High-powered angle grinder with extra high cooling capacity for fast work progress even under the toughest operating conditions
- Sturdy, durable Metabo marathon motor
- Metabo dust protection technology for extremely long service life of unit: marathon motor with winding protection grid, fully enclosed switch, labyrinth seals on the ball bearing□, ...
- Ergonomic housing design with distinctive indents for comfortably holding the device during clearing and roughing, as well as slip-proof holding of the unit
- Diecast aluminium gear unit housing: robust and resistant to wear
- Metabo S-automatic torque limiting clutch: to limit any sudden reverse torque that can occur if tools jam or get caught.
- Metabo "Quick": quick tool change without using a key - quick, comfortable and safe
- Additional vibration damping Metabo VibraTech (MVT) handle for convenient continuous operation
- The tool-free adjustment and removal of the protective cover allows you to adjust the device for any application in seconds
- Metabo winding protection grid to protect the motor from abrasive effects
- Highly durable switch-off carbon brush with dust protection housing

Comparative device characteristics

Grinding wheel Ø	125 mm
Torque	2,2 Nm
No load speed	10.000 /min
Rated input power	800 W
Output power	490 W
Rated load speed	7.000 /min
Spindle thread	M 14
Weight (without mains cable)	1,8 oz

Scope of delivery

protective cover, inner support flange, "quick" flange nut, metabo VibraTech (MVT) handle