


### 规格 Specifications

额定负荷 Ratings	DC 30 V 0.1 A
初始接触电阻 Initial Contact Resistance	50 mΩ Max.
绝缘电阻 Insulation Resistance	DC 500 V 60 Sec. 100 MΩ Min.
抗电强度 Dielectric Voltage	AC 1000 V (50~60HZ) 60 Sec.

① 操作力 Operating Force (O.F.)	25±15 gf
② 回复力 Releasing Force (R.F.)	5 gf Min.
③ 自由位置 Free Position (F.P.)	10 mm Max.
④ 动作位置 Operating Position (O.P.)	7.20±0.80 mm
⑤ 过行程 Over Travel (O.T.)	0.50 mm Min.
⑥ 差程 Movement Differential Travel (D.T.)	0.50 mm Max.
⑦ 机械寿命 Operating Life Without Load	500,000 Cycles
⑧ 负荷寿命 Operating Life With Load	50,000 Cycles



6	杠杆 LEVER	SUS	1	NATURAL
5	弹片 CONTACT SPRING	C1720	1	Ag PLATED
4	端子 TERMINAL	C2680R	3	Ag PLATED
3	胶壳 HOUSING	PBT	1	BLACK C
2	胶柄 KNOB	PBT	1	RED
1	胶盖 COVER	PBT	1	BLACK C
序号 NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS

A02	增加杠杆长度尺寸标注12.50见①		曹文斌	2006/11/21
	机械寿命1000000次变更为500000次见②			
A01	增加过行程参数0.50mm Min.见③		刘瑞富	2006-6-09
	动作位置6.80±0.80mm变更为7.20±0.80mm见④			
标号 REV	接触行程1.8mm Max. 变为自由位置10mm Max. 见⑤		刘瑞富	2006-6-09
	增加回复力参数5gf Min.见⑥			
	操作力25±10gf变更为25±15gf见⑦			
	增加行程参数0.50mm Min.见⑧			

内容 DESCRIPTION 签名 SIGN. 日期 DATE

DWG NO. ITEM2672

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE		MICRO SWITCH		ITEM NO	MS-118305-G	
UNDER 1	± 0.10	DRAWN		曹文斌	2006/11/21	VERSION	A02	PAGE 1 OF 1
1 - 10	± 0.30	REVIEWED		张念明	2006/11/22	SCALE		UNIT mm
OVER 10	± 0.50	APPROVED		刘瑞富	2006/11/23	PROJECTION		

COMAX ELECTRONICS (HUIZHOU) CO.,LTD.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Components:](#)

[MS-118305-G](#)