

PANDUIT PART NUMBER	WIRE SIZE AWG	DIMENSIONS in.		
PREFIX		±.02 A	±.01 B DIA.	±.01 C
BS18	22-18	.62 (15.7)	.14 (3.6)	.032 (0.81)
BS14	16-14	.62 (15.7)	.16 (4.1)	.032 (0.81)
BS10	12-10	.63 (16.0)	.22 (5.6)	.040 (1.02)

NOTES:



- UL LISTED AND CSA CERTIFIED FOR:
 - SOLID OR STRANDED COPPER WIRE
 - 302° F (150° C) MAX. TEMP. RATING
- MATERIAL:
 - STAMPING - COPPER, TIN PLATED
- See www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS:
 - UL LISTED AND CSA CERTIFIED:
CT-100, CT-100A, CT-200, CT-570, CT-600A,
CT-1570, CT-1701, CT-2500
 - PANDUIT APPROVED: CT-160, CT-260
- WIRE STRIP LENGTH: $9/32^{+1/32}_{-0}$ (7.1 $^{+.8}_{-.0}$)



LISTED
587H
E52164



CERTIFIED
LR31212



PANDUIT

CORP.

TINLEY PARK, ILLINOIS

NON-INSULATED BUTT SPLICE

DRAWN BY
DAW

CHK'D

SCALE
NONE

DRAWING NO.
A41338

07	8-11	SHOR		MODIFIED NOTE #3
06	4-11	SB		ADDED CT-2500, CT-600A, CT1701 TOOLS. ADDED NOTE #3
REV	DATE	BY	CHK	DESCRIPTION