



MAGNILITE® - VISION-LITE® RECTANGULAR MAGNIFIER - 25" REACH - WEIGHTED BASE

SKU# 71600

Vision-Lite® Rectangular Magnifier with 3 Diopter (1.75X) lens. Features a 25" Arm Reach and Weighted Base Assembly. **NEW** Glare Free "**FULL SPECTRUM**" Bulb for high light output. **ESD Safe.**

PRODUCT DESCRIPTION

Vision-Lite® Fully Dimmable Magnifier

The largest and clearest magnifier on the market features excellent image clarity, lighting control and energy efficiency. Made in the USA.

Our original Green-Lite®! The Vision-Lite® is the world's first and only dimmable fluorescent illuminated magnifier. "Patented" state-of-the-art microchip controlled ballast technology allows the Vision-Lite® to be dimmable from 100% down to 25%, so that highly reflective surfaces can easily be seen by dimming the units exclusive high output three-sided bulb.

- Made in the USA
- ESD safe and RoHS compliant
- Patented dimming technology for precise output control from 100% to 25%
- Shadowless wrap-around T5 bulb for uniform lighting at any level
- Crown white optical grade glass for highest resolution images
- 3 Diopter (1.75X) lens
- Rugged all metal construction
- Table edge clamp and other mounting choices
- 10 Year Mechanical Warranty...best in the business
- Also Available in 230v

SPECIFICATIONS

Name	Magnilite® - Vision-Lite® Rectangular Magnifier - 25" Reach - Weighted Base
SKU	71600
Product Line	Magnilite®
Magnification	1.75x (3 Diop)
Reach	25"
Mounting Style	Weighted Base
Voltage	120 Volt 230 Volt Optional
ESD Safe	Yes