



Search Results

Evaluate

- FAQ's
- Press Releases
- FiberRunner ..

Design a Solution

- Catalog Cut Sheet
- PDF-FRH4524X4YL
- Part Drawings
- PDF-FiberRunner ..
- Specification Sheets
- PDF-24x4 FiberRu ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-FiberRunner ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'FRH4524X4YL'

Your search criteria matched only one product, shown below

FRH4524X4YL



The complete selection of fittings feature bend radius control to prevent excessive bends in high performance copper and fiber optic cabling.

- Minimum 3" (76.2mm) bend radius control fittings
- Protect against signal loss and performance degradation
- Assemble using FRBC QuikLock™ couplers
- For other standard colors replace suffix YL (Yellow) with OR (Orange) or BL (Black)

▪ Part Number	FRH4524X4YL
▪ RoHS Compliancy Status	Compliant
▪ Product Name	24x4 Horizontal 45° Fitting
▪ Part Description	Attaches to 24x4 channel and/or fittings to create a 45° horizontal turn from a straight horizontal run.
▪ Material	ABS
▪ Color	Yellow
▪ Fitting Type	Horizontal 45°
▪ Couplers Required	(2 pcs.) FRBC24X4YL
▪ System Type	24 x 4 FiberRunner Fitting
▪ System Size	24x4
▪ CE Compliant	No
▪ Pricing Description	Fitting, Horizontal 45 Degree, 24x4, (600mmx100mm)
▪ Cover Part Number	FRH45CV24YL
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.