

FOR 5 x 20 mm FUSES

5 x 20 mm Low Amperage P.C. Board Type



APPROVALS: Recognized under the Components Program of Underwriters Laboratories and Certified by CSA.

SPECIFICATIONS:

Electrical: Rated for 3.15 amperes at 250 volts.

Dielectric Strength: 3000 volts minimum.



Terminals: Tin plated copper alloy.

Base: Gray thermoplastic with UL 94V0 flammability rating.

Ambient Temperature: 60°C maximum.

ORDERING INFORMATION:

Catalog Number	Number of Poles
354 252	1



Note: Metric dimensions are shown. Inches are in parentheses.

5 x 20 mm P.C. Board Type

SPECIFICATIONS:

Electrical: Rated for currents up to 6.3 amperes, 250 volts.



Clip/Terminals: Tin plated spring brass. Ear type.

Base: Phenolic laminate. UL 94V0 flammability rating.

Ambient Temperature: 120°C maximum.

ORDERING INFORMATION:

Catalog Number	Number of Poles
520 002	1



Note: Metric dimensions are shown. Inches are in parentheses.