




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			0	RELEASED PER EC OS13-0016-05	04-07-05	AF	JG



1 MOLDED PARTS: FLAME RETARDANT 94V-0 RATED THERMOPLASTIC, BLACK.
SHELL: CARBON STEEL
CONTACTS: PHOSPHOR BRONZE
EYELETS: BRASS
INSERTS: ZINC

△ 2 SHELL: .000100 MIN TIN OVER .000050 MIN COPPER.
CONTACTS: .000030 MIN GOLD FOR A DISTANCE OF .100 MIN FROM
MATING END, .000100 MIN TIN
ON SOLDER POST, ALL OVER .000050 MIN NICKEL.
EYELETS: .000100 MIN COPPER OVER COPPER FLASH.
INSERTS: CLEAR CHROMATE

5745984-4
PART NUMBER

**COPYRIGHT 2005
TYCO ELECTRONICS CORP
ALL RIGHTS RESERVED**

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04-07-05 A. FERNANDEZ-DOCKS OK'd 04-07-05 S. BOLASH AP'D 04-07-05 M. WALMSLEY		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RCPT ASSY, SIZE 2, RTANG, W/FRONT METAL SHELL, .026 DIA POSTS, AMP/PMITE HD-20 (.590 FOOTPRINT) SHORT LEG	
		0 PLC ± . 1 PLC ± . 2 PLC ± .005 3 PLC ± . ANGLES ± °		PRODUCT SPEC 108-40025 APPLICATION SPEC 114-40010	
MATERIAL 		FINISH 		SIZE A1	
				CAGE CODE 00779	
				DRAWING NO C-5745984	
				RESTRICTED TO	
				SCALE 4:1	
				SHEET 1 OF 1	
				REV 0	
CUSTOMER DRAWING					