



(1,27 mm) .050"

FLEXCARD™ TERMINAL & SOCKET STRIPS

Yes

Reflowed solder forced into lock notch

Plated Through-hole

Plastic Solder Lock

RV[®]
FILE NO. E111594

FCF	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	CARD SLOT	TAIL OPTION	SL

Specify LEAD STYLE from chart

PLATING OPTION

-L
μ" (0,25 μm)
old on post,
te Tin on tail

-S
 100 μ" (0,76 μm)
 Gold on post,
 Matte Tin on tail


**CARD
SLOT**

-01
= Accepts
(0,80 mm)
.031"
thick
card

TAIL OPTION

-RA
= Right Angle
(Leave blank for
vertical version.
Style -02 only)

LEAD STYLE	Y	CARD-TO-BOARD SPACE (X)
-02	(6,35) .250	(2,60) .1025
-03	(9,53) .375	(9,53) .375



EMF

1 NO. PINS
PER ROW

20, 30, 40 & 50
(Standard sizes)

CARD THICKNESS

-01
= (0,80 mm) .031"
thick board

PLATING OPTION

-L
= 10μ" (0,25 μm)
Gold on contact,
Matte Tin on tail

-S
= 30μ" (0,76 μm)
Gold on contact,
Matte Tin on tail

