





NOTE:

1. MATERIAL:

HOUSING: PA46 GLASS FILLED, UL94V-0, COLOR: NATURAL

TERMINAL: PHOSPHOR BRONZE

2. PLATING: 1) PARTIAL GOLD PLATING OVER NICKEL PLATING OVERALL

CONTACT POINT: 0.10 μm MINIMUM GOLD PLATING



TAIL POINT :GOLD PLATING

2) 1-3 μm TIN-BISMUTH OVER NICKEL PLATING OVERALL

3. PRODUCT SPECIFICATION: PS-78119-001

4. PRODUCT ARE PACKED IN TAPE & REEL.

REVISED EC NO: J2013-1512 DRW: KAYOSHI I O I 2013/06/12 CHKD: K TAKAHASHI 2013/06/12 APPR: YNOGAWA 2013/06/25	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_B=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
			mm INCH		DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT						
			4 PLACES ± --- ± ---		CHECKED BY BOKOK	DATE 2006/04/18							
			3 PLACES ± --- ± ---		APPROVED BY PTL IM	DATE 2006/04/18							
			2 PLACES ± 0.15 ± ---		DOCUMENT NO. SD-78119-001					SHEET NO. 1 OF 7			
			1 PLACE ± --- ± ---										
			0 PLACE ± ±										
			ANGULAR ± 3 °										
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					MATERIAL NO. SEE TABLE					
								SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			



N	0.30 ^{+0.05} _{-0.02}	0.30 ^{+0.05} _{-0.02}	0.35 ^{+0.04} _{-0.03}	0.35 ^{+0.05} ₀
P	0.50±0.03	0.50±0.05	0.50±0.02	0.50±0.05
M	0.50±0.10	0.50±0.08	0.50±0.12	0.50±0.10
B	B±0.03	B±0.05	B±0.03	B±0.05
	1	2	1	2
	FFC		FPC	

REVISED EC NO: J2013-1512 DRWN: KAWASHI 101 2013/06/12 CHKD: KATAHASHI 2013/06/12 APPR: YNOGAWA 2013/06/25	DESCRIPTION	QUALITY SYMBOLS FA=0 FG=0 FP=0	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			4 PLACES	mm	INCH	DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT	molex				
				3 PLACES	± ---	± ---	CHECKED BY BOKOK			DATE 2006/04/18			
				2 PLACES	± 0.15	± ---	APPROVED BY PTLIM			DATE 2006/04/18			
				1 PLACE	± ---	± ---	MATERIAL NO.			DOCUMENT NO.	SHEET NO.		
				0 PLACE	±	±	SEE TABLE			SD-78119-001	2 OF 7		
			A4	REV		ANGULAR ± 3 °							
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

10 9 8 7 6 5 4 3 2 1

ELV & RoHS COMPLIANT

TIN-BISMUTH PLATING TERMINAL ASSEMBLY PART NUMBERS

ASSY P/N W/O PACKAGING	CKT	DIM A	DIM B	DIM C	DIM D	PLATING TYPE
78119-0109	10	7.10	4.50	6.40	5.60	2
78119-0119	11	7.60	5.00	6.90	6.10	
78119-0129	12	8.10	5.50	7.40	6.60	
78119-0139	13	8.60	6.00	7.90	7.10	
78119-0149	14	9.10	6.50	8.40	7.60	
78119-0159	15	9.60	7.00	8.90	8.10	
78119-0169	16	10.10	7.50	9.40	8.60	
78119-0179	17	10.60	8.00	9.90	9.10	
78119-0189	18	11.10	8.50	10.40	9.60	
78119-0199	19	11.60	9.00	10.90	10.10	
78119-0209	20	12.10	9.50	11.40	10.60	
78119-0219	21	12.60	10.00	11.90	11.10	
78119-0229	22	13.10	10.50	12.40	11.60	
78119-0239	23	13.60	11.00	12.90	12.10	
78119-0249	24	14.10	11.50	13.40	12.60	
78119-0259	25	14.60	12.00	13.90	13.10	
78119-0269	26	15.10	12.50	14.40	13.60	
78119-0279	27	15.60	13.00	14.90	14.10	
78119-0289	28	16.10	13.50	15.40	14.60	
78119-0299	29	16.60	14.00	15.90	15.10	
78119-0309	30	17.10	14.50	16.40	15.60	

ASSY P/N W/O PACKAGING	CKT	DIM A	DIM B	DIM C	DIM D	PLATING TYPE
78119-0319	31	17.60	15.00	16.90	16.10	2
78119-0329	32	18.10	15.50	17.40	16.60	
78119-0339	33	18.60	16.00	17.90	17.10	
78119-0349	34	19.10	16.50	18.40	17.60	
78119-0359	35	19.60	17.00	18.90	18.10	
78119-0369	36	20.10	17.50	19.40	18.60	
78119-0379	37	20.60	18.00	19.90	19.10	
78119-0389	38	21.10	18.50	20.40	19.60	
78119-0399	39	21.60	19.00	20.90	20.10	
78119-0409	40	22.10	19.50	21.40	20.60	

REVISED	EC NO: J2013-1512	2013/06/12	QUALITY SYMBOLS
	DRWNA:YOSHI I01	2013/06/12	
	CHKD:K TAKAHASHI	2013/06/12	
	APPR:YNOGAWA	2013/06/25	
A4	DESCRIPTION		REV

$\nabla_A = 0$
 $\nabla_C = 0$
 $\nabla_P = 0$



GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	$\pm$ ---	$\pm$ ---
3 PLACES	$\pm$ ---	$\pm$ ---
2 PLACES	$\pm$ 0.15	$\pm$ ---
1 PLACE	$\pm$ ---	$\pm$ ---
0 PLACE	$\pm$	$\pm$
ANGULAR $\pm$ 3 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
YLQIAO	2006/04/11
CHECKED BY	DATE
BOKOK	2006/04/18
APPROVED BY	DATE
PTL IM	2006/04/18
MATERIAL NO.	
SEE TABLE	
SIZE	
A3	

SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
TITLE		
0.50MM PITCH, FPC CONN. NON-ZIF, SMT		
molex		
DOCUMENT NO.		SHEET NO.
SD-78119-001		4 OF 7
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

9 8 7 6 5 4 3 2 1



EMBOSSED TYPE A

CUSTOMER
PULL OUT DIRECTION

REEL

NOTES:



1. LEADER AND TRAILER TAPE

2. PEELING OFF FORCE OF THE TOP TAPE: 20-80gf.
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)

3. PACKAGING STANDARD IS AS PER EIA-481.


4. TAPE & REEL QUANTITY = 1000 PCS/REEL

SECTION Y-Y




DETAIL 1

EMBOSSED TYPE B



DETAIL 1



SECTION Z-Z

REVISED EC NO: J2013-1512 DRWN:AYOSHI/01 CHKD:K TAKAHASHI APPR: YNOGAWA REV A4	DESCRIPTION 2013/06/12 2013/06/12 2013/06/25	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY YUQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT			
			4 PLACES	± ---	± ---	CHECKED BY BOKOK	DATE 2006/04/18				
			3 PLACES	± ---	± ---	APPROVED BY PTL IM		DATE 2006/04/18			
			2 PLACES	± 0.15	± ---						
			1 PLACE	± ---	± ---						
			0 PLACE	±	±	MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-78119-001				5 OF 7		
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																										
	ELV & RoHS COMPLIANT																																																																																																																																																																																																																																																																																																			
F											F																																																																																																																																																																																																																																																																																									
E	PARTIAL GOLD PLATING TERMINAL ASSEMBLY PART NUMBERS										E																																																																																																																																																																																																																																																																																									
D	<table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1108</td><td>78119-0108</td><td>10</td><td>24.00</td><td>-</td><td>11.50</td><td>7.40</td><td>5.10</td><td rowspan="10">A</td></tr><tr><td>78119-1118</td><td>78119-0118</td><td>11</td><td>24.00</td><td>-</td><td>11.50</td><td>7.90</td><td>5.60</td></tr><tr><td>78119-1128</td><td>78119-0128</td><td>12</td><td>24.00</td><td>-</td><td>11.50</td><td>8.40</td><td>6.10</td></tr><tr><td>78119-1138</td><td>78119-0138</td><td>13</td><td>24.00</td><td>-</td><td>11.50</td><td>8.90</td><td>6.60</td></tr><tr><td>78119-1148</td><td>78119-0148</td><td>14</td><td>24.00</td><td>-</td><td>11.50</td><td>9.40</td><td>7.10</td></tr><tr><td>78119-1158</td><td>78119-0158</td><td>15</td><td>24.00</td><td>-</td><td>11.50</td><td>9.90</td><td>7.60</td></tr><tr><td>78119-1168</td><td>78119-0168</td><td>16</td><td>24.00</td><td>-</td><td>11.50</td><td>10.40</td><td>8.10</td></tr><tr><td>78119-1178</td><td>78119-0178</td><td>17</td><td>24.00</td><td>-</td><td>11.50</td><td>10.90</td><td>8.60</td></tr><tr><td>78119-1188</td><td>78119-0188</td><td>18</td><td>24.00</td><td>-</td><td>11.50</td><td>11.40</td><td>9.10</td></tr><tr><td>78119-1198</td><td>78119-0198</td><td>19</td><td>24.00</td><td>-</td><td>11.50</td><td>11.90</td><td>9.60</td></tr><tr><td>C</td><td>78119-1208</td><td>20</td><td>24.00</td><td>-</td><td>11.50</td><td>12.40</td><td>10.10</td><td rowspan="10">B</td></tr><tr><td>78119-1218</td><td>78119-0218</td><td>21</td><td>32.00</td><td>28.40</td><td>14.20</td><td>12.90</td><td>10.60</td></tr><tr><td>78119-1228</td><td>78119-0228</td><td>22</td><td>32.00</td><td>28.40</td><td>14.20</td><td>13.40</td><td>11.10</td></tr><tr><td>78119-1238</td><td>78119-0238</td><td>23</td><td>32.00</td><td>28.40</td><td>14.20</td><td>13.90</td><td>11.60</td></tr><tr><td>78119-1248</td><td>78119-0248</td><td>24</td><td>32.00</td><td>28.40</td><td>14.20</td><td>14.40</td><td>12.10</td></tr><tr><td>78119-1258</td><td>78119-0258</td><td>25</td><td>32.00</td><td>28.40</td><td>14.20</td><td>14.90</td><td>12.60</td></tr><tr><td>78119-1268</td><td>78119-0268</td><td>26</td><td>32.00</td><td>28.40</td><td>14.20</td><td>15.40</td><td>13.10</td></tr><tr><td>78119-1278</td><td>78119-0278</td><td>27</td><td>32.00</td><td>28.40</td><td>14.20</td><td>15.90</td><td>13.60</td></tr><tr><td>B</td><td>78119-1288</td><td>28</td><td>32.00</td><td>28.40</td><td>14.20</td><td>16.40</td><td>14.10</td><td rowspan="2"></td></tr><tr><td>78119-1298</td><td>78119-0298</td><td>29</td><td>32.00</td><td>28.40</td><td>14.20</td><td>16.90</td><td>14.60</td></tr><tr><td>78119-1308</td><td>78119-0308</td><td>30</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.40</td><td>15.10</td><td></td></tr><td colspan="8"></td><td colspan="4"><table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1318</td><td>78119-0318</td><td>31</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.90</td><td>15.60</td><td rowspan="11">B</td></tr><tr><td>78119-1328</td><td>78119-0328</td><td>32</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.40</td><td>16.10</td></tr><tr><td>78119-1338</td><td>78119-0338</td><td>33</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.90</td><td>16.60</td></tr><tr><td>78119-1348</td><td>78119-0348</td><td>34</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.40</td><td>17.10</td></tr><tr><td>78119-1358</td><td>78119-0358</td><td>35</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.90</td><td>17.60</td></tr><tr><td>78119-1368</td><td>78119-0368</td><td>36</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.40</td><td>18.10</td></tr><tr><td>78119-1378</td><td>78119-0378</td><td>37</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.90</td><td>18.60</td></tr><tr><td>78119-1388</td><td>78119-0388</td><td>38</td><td>32.00</td><td>28.40</td><td>14.20</td><td>21.40</td><td>19.10</td></tr><tr><td>78119-1398</td><td>78119-0398</td><td>39</td><td>44.00</td><td>40.40</td><td>20.20</td><td>21.90</td><td>19.60</td></tr><tr><td>78119-1408</td><td>78119-0408</td><td>40</td><td>44.00</td><td>40.40</td><td>20.20</td><td>22.40</td><td>20.10</td></tr></table></td><td></td></table>								ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE	78119-1108	78119-0108	10	24.00	-	11.50	7.40	5.10	A	78119-1118	78119-0118	11	24.00	-	11.50	7.90	5.60	78119-1128	78119-0128	12	24.00	-	11.50	8.40	6.10	78119-1138	78119-0138	13	24.00	-	11.50	8.90	6.60	78119-1148	78119-0148	14	24.00	-	11.50	9.40	7.10	78119-1158	78119-0158	15	24.00	-	11.50	9.90	7.60	78119-1168	78119-0168	16	24.00	-	11.50	10.40	8.10	78119-1178	78119-0178	17	24.00	-	11.50	10.90	8.60	78119-1188	78119-0188	18	24.00	-	11.50	11.40	9.10	78119-1198	78119-0198	19	24.00	-	11.50	11.90	9.60	C	78119-1208	20	24.00	-	11.50	12.40	10.10	B	78119-1218	78119-0218	21	32.00	28.40	14.20	12.90	10.60	78119-1228	78119-0228	22	32.00	28.40	14.20	13.40	11.10	78119-1238	78119-0238	23	32.00	28.40	14.20	13.90	11.60	78119-1248	78119-0248	24	32.00	28.40	14.20	14.40	12.10	78119-1258	78119-0258	25	32.00	28.40	14.20	14.90	12.60	78119-1268	78119-0268	26	32.00	28.40	14.20	15.40	13.10	78119-1278	78119-0278	27	32.00	28.40	14.20	15.90	13.60	B	78119-1288	28	32.00	28.40	14.20	16.40	14.10		78119-1298	78119-0298	29	32.00	28.40	14.20	16.90	14.60	78119-1308	78119-0308	30	32.00	28.40	14.20	17.40	15.10										<table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1318</td><td>78119-0318</td><td>31</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.90</td><td>15.60</td><td rowspan="11">B</td></tr><tr><td>78119-1328</td><td>78119-0328</td><td>32</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.40</td><td>16.10</td></tr><tr><td>78119-1338</td><td>78119-0338</td><td>33</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.90</td><td>16.60</td></tr><tr><td>78119-1348</td><td>78119-0348</td><td>34</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.40</td><td>17.10</td></tr><tr><td>78119-1358</td><td>78119-0358</td><td>35</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.90</td><td>17.60</td></tr><tr><td>78119-1368</td><td>78119-0368</td><td>36</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.40</td><td>18.10</td></tr><tr><td>78119-1378</td><td>78119-0378</td><td>37</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.90</td><td>18.60</td></tr><tr><td>78119-1388</td><td>78119-0388</td><td>38</td><td>32.00</td><td>28.40</td><td>14.20</td><td>21.40</td><td>19.10</td></tr><tr><td>78119-1398</td><td>78119-0398</td><td>39</td><td>44.00</td><td>40.40</td><td>20.20</td><td>21.90</td><td>19.60</td></tr><tr><td>78119-1408</td><td>78119-0408</td><td>40</td><td>44.00</td><td>40.40</td><td>20.20</td><td>22.40</td><td>20.10</td></tr></table>				ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE	78119-1318	78119-0318	31	32.00	28.40	14.20	17.90	15.60	B	78119-1328	78119-0328	32	32.00	28.40	14.20	18.40	16.10	78119-1338	78119-0338	33	32.00	28.40	14.20	18.90	16.60	78119-1348	78119-0348	34	32.00	28.40	14.20	19.40	17.10	78119-1358	78119-0358	35	32.00	28.40	14.20	19.90	17.60	78119-1368	78119-0368	36	32.00	28.40	14.20	20.40	18.10	78119-1378	78119-0378	37	32.00	28.40	14.20	20.90	18.60	78119-1388	78119-0388	38	32.00	28.40	14.20	21.40	19.10	78119-1398	78119-0398	39	44.00	40.40	20.20	21.90	19.60	78119-1408	78119-0408	40	44.00	40.40	20.20	22.40	20.10	
ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE																																																																																																																																																																																																																																																																																												
78119-1108	78119-0108	10	24.00	-	11.50	7.40	5.10	A																																																																																																																																																																																																																																																																																												
78119-1118	78119-0118	11	24.00	-	11.50	7.90	5.60																																																																																																																																																																																																																																																																																													
78119-1128	78119-0128	12	24.00	-	11.50	8.40	6.10																																																																																																																																																																																																																																																																																													
78119-1138	78119-0138	13	24.00	-	11.50	8.90	6.60																																																																																																																																																																																																																																																																																													
78119-1148	78119-0148	14	24.00	-	11.50	9.40	7.10																																																																																																																																																																																																																																																																																													
78119-1158	78119-0158	15	24.00	-	11.50	9.90	7.60																																																																																																																																																																																																																																																																																													
78119-1168	78119-0168	16	24.00	-	11.50	10.40	8.10																																																																																																																																																																																																																																																																																													
78119-1178	78119-0178	17	24.00	-	11.50	10.90	8.60																																																																																																																																																																																																																																																																																													
78119-1188	78119-0188	18	24.00	-	11.50	11.40	9.10																																																																																																																																																																																																																																																																																													
78119-1198	78119-0198	19	24.00	-	11.50	11.90	9.60																																																																																																																																																																																																																																																																																													
C	78119-1208	20	24.00	-	11.50	12.40	10.10	B																																																																																																																																																																																																																																																																																												
78119-1218	78119-0218	21	32.00	28.40	14.20	12.90	10.60																																																																																																																																																																																																																																																																																													
78119-1228	78119-0228	22	32.00	28.40	14.20	13.40	11.10																																																																																																																																																																																																																																																																																													
78119-1238	78119-0238	23	32.00	28.40	14.20	13.90	11.60																																																																																																																																																																																																																																																																																													
78119-1248	78119-0248	24	32.00	28.40	14.20	14.40	12.10																																																																																																																																																																																																																																																																																													
78119-1258	78119-0258	25	32.00	28.40	14.20	14.90	12.60																																																																																																																																																																																																																																																																																													
78119-1268	78119-0268	26	32.00	28.40	14.20	15.40	13.10																																																																																																																																																																																																																																																																																													
78119-1278	78119-0278	27	32.00	28.40	14.20	15.90	13.60																																																																																																																																																																																																																																																																																													
B	78119-1288	28	32.00	28.40	14.20	16.40	14.10																																																																																																																																																																																																																																																																																													
78119-1298	78119-0298	29	32.00	28.40	14.20	16.90	14.60																																																																																																																																																																																																																																																																																													
78119-1308	78119-0308	30	32.00	28.40	14.20	17.40	15.10																																																																																																																																																																																																																																																																																													
ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE																																																																																																																																																																																																																																																																																												
78119-1318	78119-0318	31	32.00	28.40	14.20	17.90	15.60	B																																																																																																																																																																																																																																																																																												
78119-1328	78119-0328	32	32.00	28.40	14.20	18.40	16.10																																																																																																																																																																																																																																																																																													
78119-1338	78119-0338	33	32.00	28.40	14.20	18.90	16.60																																																																																																																																																																																																																																																																																													
78119-1348	78119-0348	34	32.00	28.40	14.20	19.40	17.10																																																																																																																																																																																																																																																																																													
78119-1358	78119-0358	35	32.00	28.40	14.20	19.90	17.60																																																																																																																																																																																																																																																																																													
78119-1368	78119-0368	36	32.00	28.40	14.20	20.40	18.10																																																																																																																																																																																																																																																																																													
78119-1378	78119-0378	37	32.00	28.40	14.20	20.90	18.60																																																																																																																																																																																																																																																																																													
78119-1388	78119-0388	38	32.00	28.40	14.20	21.40	19.10																																																																																																																																																																																																																																																																																													
78119-1398	78119-0398	39	44.00	40.40	20.20	21.90	19.60																																																																																																																																																																																																																																																																																													
78119-1408	78119-0408	40	44.00	40.40	20.20	22.40	20.10																																																																																																																																																																																																																																																																																													
A	<table><tr><td rowspan="10">REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 CHKD: K TAKAHASHI APPR: YNOGAWA 2013/06/12 2013/06/12 2013/06/15</td><td rowspan="10">DESCRIPTION QUALITY SYMBOLS F_A=0 F_C=0 F_P=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2" rowspan="10">THIRD ANGLE PROJECTION</td><td rowspan="10">TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT molex SD-78119-001</td><td rowspan="10">DOCUMENT NO. SHEET NO. 6 OF 7</td></tr><tr><td>4 PLACES</td><td>± --- ± ---</td><td>DRAWN BY YLQIAO</td><td>DATE 2006/04/11</td><td colspan="6" rowspan="9">SEE TABLE</td></tr><tr><td>3 PLACES</td><td>± --- ± ---</td><td>CHECKED BY BOKOK</td><td>DATE 2006/04/18</td></tr><tr><td>2 PLACES</td><td>± 0.15 ± ---</td><td>APPROVED BY PTL IM</td><td>DATE 2006/04/18</td></tr><tr><td>1 PLACE</td><td>± --- ± ---</td><td colspan="8" rowspan="2">MATERIAL NO.</td></tr><tr><td colspan="2"></td><td>0 PLACE</td><td>± ±</td></tr><tr><td colspan="2"></td><td colspan="3">ANGULAR ± 3 °</td><td colspan="7"></td></tr><tr><td colspan="2"></td><td colspan="3">DRAFT WHERE APPLICABLE</td><td colspan="7"></td></tr><tr><td colspan="2"></td><td colspan="3">MUST REMAIN</td><td colspan="7"></td></tr><tr><td colspan="2"></td><td colspan="3">WITHIN DIMENSIONS</td><td colspan="7"></td></tr></table>										REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 CHKD: K TAKAHASHI APPR: YNOGAWA 2013/06/12 2013/06/12 2013/06/15	DESCRIPTION QUALITY SYMBOLS F _A =0 F _C =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT molex SD-78119-001	DOCUMENT NO. SHEET NO. 6 OF 7	4 PLACES	± --- ± ---	DRAWN BY YLQIAO	DATE 2006/04/11	SEE TABLE						3 PLACES	± --- ± ---	CHECKED BY BOKOK	DATE 2006/04/18	2 PLACES	± 0.15 ± ---	APPROVED BY PTL IM	DATE 2006/04/18	1 PLACE	± --- ± ---	MATERIAL NO.										0 PLACE	± ±			ANGULAR ± 3 °												DRAFT WHERE APPLICABLE												MUST REMAIN												WITHIN DIMENSIONS																																																																																																																																																																																																							
REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 CHKD: K TAKAHASHI APPR: YNOGAWA 2013/06/12 2013/06/12 2013/06/15	DESCRIPTION QUALITY SYMBOLS F _A =0 F _C =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT molex SD-78119-001			DOCUMENT NO. SHEET NO. 6 OF 7																																																																																																																																																																																																																																																																																							
		4 PLACES	± --- ± ---	DRAWN BY YLQIAO	DATE 2006/04/11	SEE TABLE																																																																																																																																																																																																																																																																																														
		3 PLACES	± --- ± ---	CHECKED BY BOKOK	DATE 2006/04/18																																																																																																																																																																																																																																																																																															
		2 PLACES	± 0.15 ± ---	APPROVED BY PTL IM	DATE 2006/04/18																																																																																																																																																																																																																																																																																															
		1 PLACE	± --- ± ---	MATERIAL NO.																																																																																																																																																																																																																																																																																																
														0 PLACE	± ±																																																																																																																																																																																																																																																																																					
				ANGULAR ± 3 °																																																																																																																																																																																																																																																																																																
				DRAFT WHERE APPLICABLE																																																																																																																																																																																																																																																																																																
				MUST REMAIN																																																																																																																																																																																																																																																																																																
				WITHIN DIMENSIONS																																																																																																																																																																																																																																																																																																
ib_frame_A3_P_AM_T Rev. G 2012/01/11																																																																																																																																																																																																																																																																																																				
	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																											

