

SERIES 1117 - SNAP-ACTION SWITCHES

TO 16 (6) A 400 V AC



PRODUCT FEATURES

- ◆ Double interrupting jump contact switching system
- ◆ Contact distance > 3 mm
- ◆ Material conformant with the filament wire test acc. to IEC 60 335-1:2001 chap. 30 and UL 94 V-0
- ◆ Large overtravel
- ◆ Actuator can be approached from all directions
- ◆ Normally open contact and normally closed contact versions

ON REQUEST

- ◆ Customized versions
- ◆ Changeover basic type 1116

Mechanical life endurance	10E4	
Contact resistance (new condition)	< 100 mOhm (1 A 12 V DC)	
Insulation resistance (new condition)	> 100 MOhm (500 V DC)	
Proof tracking	250 PTI	
Protection type	IP 40	
Ambient temperature	-40 °C ... +85 °C	
Flammability	UL 94 V-0	
Glow wire test temperature	850 °C	
Material	actuator housing terminals	PA glass fiber-reinforced PA glass fiber-reinforced silver plated
Contact material	Ag	
Contact distance	≥ 3 mm	
Approval marks	 /  / 	
Suitable for appliances of protection class II under compliance with the installation conditions required on the equipment side		




SERIES 1117 - SNAP-ACTION SWITCHES

TO 16 (6) A 400 V AC

	16 (6) A 400 V AC 1E4	12 A 250 V AC 1/2 HP	12 A 125 V AC 1/6 HP	Terminal type	Terminal description	Contact distance in mm	Operating force in N	Operating position (OP) in mm	Difference travel max. in mm	Free position (FP) max. in mm	Permissible total travel position (TP) in mm	Stock version
Normally closed contact (SPNC)												
1117.0206	●	●	●		6.3	≥ 3	3.5 ± 0.5	12.4 ± 0.5	2.6	15.2	8.5	●
Normally open contact (SPNO)												
1117.0106	●	●	●		6.3	≥ 3	3.5 ± 0.5	12.4 ± 0.5	2.6	15.2	8.5	●



Basic type 1117



 Quick-connect terminal
6.3 x 0.8

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

TACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES

SENSORS