


ED1550/X (3.5 mm) EDZ1550/X (3.81 mm)



2-20(16) poles, Spacing 3.5 mm or 3.81 mm
insert required no. of poles **x**
How to order see page 5



Ratings:

Rated Voltage	300 V	160 V
Rated Current	8 A	9 A (T60)
Wire Size	AWG 28-16	1.5 mm ²
Test Voltage		4 kV/3
Rated Torque/ScrewSize		0.4 Nm/M2

Max. Rated Cross Section

Single Wire (solid)	1.5 mm ²
Stranded Wire (flexible)	1.0 mm ²
Stranded wire with Ferrules	1.0 mm ²

Dimensions

Spacing	3.5 mm (3.81 mm)
Stripped Length	7.0 mm

Materials

Insulating Material	PA
Flammability Class	UL94 V-0
Temperature Range	-30°C/+105°C
Terminal Block	CuZn
Contact	CuSn

Color

Green

