

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1203410150

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Micro-Change M12 CAT6A Back Panel-Mount Receptacle, 8 Poles, Female (Straight), 0.0185m (.728") Length



Documents:

Drawing (PDF)

Packaging Specification PK-120341-075 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Receptacles
Series	120341
IP Rating	IP67
Overview	Brad Industrial Ethernet Solutions
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A
Type	PCB Mount
UPC	884982937666
Physical	
Coupling Type	Internal Thread
Gender	Female
Keyway	X-coded
Length	0.0185m
Material - Component	Polyamide
Mounting Thread Size	M12 x 1.0
Net Weight	18.143/g
Orientation	Straight
Panel Mount	Back
Poles	8
Temperature Range - Operating	-40°C to +85°C
Wire Size AWG	N/A
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	48V
Material Info	
Engineering Number	ER2D2U703
Reference - Drawing Numbers	
Packaging Specification	PK-120341-075
Sales Drawing	1203410150-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)4578-DC (25 June 2020)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120341 Series

Mates With

120341 Micro-Change CAT6A Cable Assemblies

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION