





REV.	DATE	DESCRIPTION
A	03/27/05	UPDATE DRAWING FORMAT



RECOMMENDED
MOUNTING HOLE

6.35 HEX NUT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex								
8						DRAWN	G.R.S.						03/27/D5			
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED		PART DESCRIPTION								
6						ISSUED		SMB BULKHEAD JACK TO JACK ADAPTER								
5					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET	1 OF 1		PART NO.							
4						CAD FILE			142250							
3	CONTACT PIN	BRASS	GOLD	1		C:/142/142250.DWG			DWG. NO.	142250.DWG	REV.	A	SIZE	A	SCALE	NA
2	INSULATDR	TEFLON	NATURAL	1												
1	BODY	BRASS	GOLD	1												
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING											