

XTRAFLEX Liquidtight Conduit Tubing & Fittings

T&B Catalog Number:

UPC Number:

LTC050GY

Status:

78621088076

Description:

Active

1/2 in. gray non-metallic Type B commercial grade liquidtight conduit.

Features

Fast installation, even in tight or cramped spaces.

Application

UL Listed for direct burial

General

Material	PVC
Color	Gray
Working Temperatures	-18 C to +105 C

Dimension Information

Size (inches)	1/2
I.D. - Minimum (inches)	0.622
I.D. - Maximum (inches)	0.642
O.D. - Minimum (inches)	0.82
O.D. - Maximum (inches)	0.84

Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	14.3 lbs. per 100

Application Support

MSDS Number	msds-0023-tb2
Guide to Nonmetallic Conduit Applications	Available on Website
XTRAFLEX System Specifications	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 95745

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com