



AMP WIRE RANGE		E13288 Listed
16-14HD AWG STRANDED		16-14HD AWG STRANDED
LR7189 Certified		MILITARY P/N AND CLASS
NOT CERTIFIED		NOT APPLICABLE

1 STAMP AMP 16-14HD* APPROX AS SHOWN

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. FOR THE LATEST REVISION, CONTACT THE AMP INCORPORATED CUSTOMER SERVICE CENTER.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm FINISHES— TOLERANCES ON : 2 PLC DEC # - 3 PLC DEC # - ANGLES # - MATERIAL COPPER PER ASTM B-152 ANNEALED		DR 1-26-93 GL KRUPPER CHK 1-26-93 DA PATTERSON APPD 1-26-93 DE MILLER APPD 1-26-93 JL MECKLEY PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE CAGE CODE DRAWING NO	
FINISH TIN PLATE 0.00254L.0001001 MIN THK PER MIL-T-10727				TERMINAL, RING TONGUE, HEAVY DUTY, BUDGET	
		SCALE 8:1		SHEET 1 OF 1	