


RECOMMENDED PCB LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. RATING: 50mA @12VDC
4. OPERATING FORCE: 260±50gf
5. TRAVEL: 0.25 +0.2/-0.1mm
6. CONTACT RESISTANCE: 100 milli-ohm max.
7. ELECTRICAL LIFE: 100,000 cycles
8. CARRIER IS FOLDED EVERY 25 PITCHES
(24 SWITCHES PER FOLD)
9. 1,000 SWITCHES PER BOX

E-SWITCH®			
TITLE			
TL 59 F260 Q			
A	10743	RELEASED FOR PRODUCTION	7/10/00
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE			
2:1			
DATE			
7/10/00			
DR			
MM			
DWG			
P010584			
REV			
A			