




SPECIFICATIONS

FREQUENCY RANGE: 2 TO 500 MHz
 NUMBER OF OUTPUT PORTS: 4
 MINIMUM ISOLATION: 22 dB
 MAXIMUM VSWR: 1.35
 MAXIMUM INSERTION LOSS: 1.50 dB



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE2001

DES.

**BNC FEMALE POWER DIVIDER FREQUENCY
 RANGE: 2-500 MHz 4 OUTPUT PORTS**

REV. A

FSCM NO. 53919

CAD FILE

100407

SCALE N/A

SIZE A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.