

# リフトドア金具

## LIFT DOOR FITTINGS


**FD-1071**  
ステンレス製
**FD-71**  
鉄製

## 特徴 Feature

PAT.PEND.

- 縦枠に取付けられる省スペース設計です。
- ユニット化しており取付けが簡単です。
- It is so designed that the product can be installed on the vertical frame.
- Installation is easy because product is one whole unit.

仕様・材質: [FD-1071]

ステンレス鋼板(SUS304)

[FD-71]

冷間圧延鋼板(SPCC)

表面仕上: [FD-1071]

光沢バレル研磨

[FD-71]

亜鉛めっきクロメート処理(MFZn-C)

用途: ●バス・特装車・製造装置等のリッド

納期: ●標準品...納期お問合せください

備考: ●扉の剛性が低い場合や開口幅が大きい場合は、補強用連結プラケットに指定の角パイプを連結してください。

●取手等は扉中央部に配置してください。

●ハンドルのご使用はAP-883(407ページ)、A-873(398ページ)等、C-1851(1165ページ)のドアキャッチ、C-878(1177ページ)コントロールセンター等の使用例を参考にしてください。

Specifications: ●Material: [FD-1071]  
Stainless steel (SUS304)

[FD-71]

Cold rolled steel plate (SPCC)

●Finish: [FD-1071]

Gross barrel polishing

[FD-71]


Zinc plating chromate treatment  
(MFZn-C)

Specificuse: ●The lid of busses, specially equipped vehicles.

Remarks: ●When the stiffness of the door is low or the width of the opening is large, connect the specified square pipe to the reinforcing connecting bracket.

●Place the handle, etc., in the center of the door.  
●Refer to the application examples for handles AP-883 (page 407) and A-873 (page 398), door catches C-1851 (page 1165) and center controls C-878 (page 1177).

FD-71



商品番号 Product No.	材質 Material	RoHS 2D/3D	CAD 2D	(L <sub>1</sub> )	L <sub>2</sub>	(H <sub>1</sub> )	(H <sub>2</sub> )	(H <sub>3</sub> )	H <sub>4</sub>	P <sub>1</sub>	P <sub>2</sub>	P <sub>3</sub>	P <sub>4</sub>	P <sub>5</sub>	P <sub>6</sub>	P <sub>7</sub>	P <sub>8</sub>	参考扉質量(kg) Reference door mass	製品質量(kg) Mass	コード Code	単価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price
FD-1071-1-30K	SUS	● 2D/3D	● 2D	564	600	305	113	90	25	140	140	140	12	15	/	9.6	290	30±1	10.5	64226	¥115,000	5個~	¥110,400
FD-1071-1-15K	SUS	● 2D/3D	● 2D	564	600	305	113	90	25	140	140	140	12	15	/	9.6	290	15±1	10.5	64225	¥115,000	5個~	¥110,400
FD-1071-2-8K	SUS	● 2D	● 2D	293	300	161	57	88	35	72	47	59	22	13.5	25	10.6	130	8±1	5.5	64228	¥85,000	5個~	¥81,600
FD-71-1-30K	SPCC	● 2D/3D	● 2D	564	600	305	113	90	25	140	140	140	12	15	/	9.6	290	30±1	10.5	64224	¥80,000	5個~	¥76,800
FD-71-1-15K	SPCC	● 2D	● 2D	564	600	305	113	90	25	140	140	140	12	15	/	9.6	290	15±1	10.5	64223	¥80,000	5個~	¥76,800
FD-71-2-8K	SPCC	● 2D/3D	● 2D	293	300	161	57	88	35	72	47	59	22	13.5	25	10.6	130	8±1	5.5	64227	¥65,000	5個~	¥62,400

価格は、(L、R) 1セットです。The price is set of left and right.

※大量のご注文は更にお安くなります。

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。



FD

ベンチ  
レーター

庫内灯

ミエール  
カーテン

サニードア

SLIDING DOOR

特装周辺  
機器

トランク

