

Search within category

GO

BUY NOW

DESIGN / INSTALL

Overall Length (ft.)	1000
Overall Length (m)	305
Jacket Material	100% low-smoke, flame retardant PVC
Conductor Gauge (AWG)	23
Nominal Diameter (In.)	0.29
Nominal Diameter (mm)	7.36
Number of Pairs	4
Package Type	Reel
Color	White
Flammability Rating	Plenum (CMP)
Length (ft.)	1000
Application	Stacking switches and switch-to-switch links, Storage area networks, Aggregation of Gigabit Ethernet channels, Real-time intensive financial transactions, Streaming video, Animation, Scientific modeling and Medical imaging
Cable Type	U/FTP
Nominal Cable Outside Diameter (In.)	0.290
Nominal Cable Outside Diameter (mm)	7.4
Part Features	Third party tested, Additional feature and benefit, Cross-divider, Reduced attenuation, Easy payout carton, Tested beyond the standards and Descending length cable markings.
Performance Level	Category 6A
Weight (Kg)	25.37
Weight (lb)	56/1000 ft.
RoHS Compliancy Status	Compliant
Min. Order Qty.	5,000