


Sta-Kon Terminal Products and Tools

Nylon-Insulated Fork Terminals

- Fork terminals enable easy installation because the mounting screw does not have to be completely removed
- Brazed seam barrel is serrated for high pull-out value. Terminal is high conductivity electrolytic copper, electro-tin plated. Insulation is color-coded
- Vinyl insulated fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wire's flex point
- Suffix "X" indicates an expanded insulation support, meaning a wider wire entry to accommodate heavy wall insulation




Nylon-Insulated Fork



CAT. NO.	PKG. QTY.	WIRE RANGE	MAX. INS.	BOLT HOLE	REC. TOOL	DIMENSIONS				STOCK THICK.
						A	B	C	M	
RA18-6F	100	22-16	.136	#6	ERG 2001	.83	.25	.25	.71	.02
RA1103	1,000	22-16	.136	#6		.83	.25	.25	.71	
RA18-8F	100	22-16	.136	#8		.86	.31	.25	.71	
RA1123	1,000	22-16	.136	#8		.86	.31	.25	.71	
RA18-10F	100	22-16	.136	#10		.86	.31	.25	.71	
RA1153	1,000	22-16	.136	#10		.86	.31	.25	.71	
RA18-14F	100	22-16	.136	1/4"		.95	.44	.31	.70	.03
RA1163	1,000	22-16	.136	1/4"		.95	.44	.31	.70	
RB14-6F	100	18-14	.162	#6		.87	.31	.25	.71	
RB1113	1,000	18-14	.162	#6		.87	.31	.25	.71	
RB14-8F	100	18-14	.162	#8		.87	.31	.25	.71	
RB1123	1,000	18-14	.162	#8		.87	.31	.25	.71	
RB14-10F	100	18-14	.162	#10	ERG 2001	.87	.38	.25	.71	.04
RB1153	1,000	18-14	.162	#10		.87	.38	.25	.71	
RB14-14F	100	18-14	.162	1/4"		.95	.44	.28	.74	
RB1163	1,000	18-14	.162	1/4"		.95	.44	.28	.74	
RB1103	1,000	18-14	.162	#6		.74	.28	.16	.60	
RB1124	1,000	18-14	.190	#8		.95	.31	.25	.79	
RB1154	1,000	18-14	.190	#10		.95	.31	.25	.79	
RC10-6F	50	12-10	.210	#6		.97	.31	.27	.81	.04
RC1113	500	12-10	.210	#6		.97	.31	.27	.81	
RC10-8F	50	12-10	.210	#8		1.00	.37	.27	.81	
RC1123	500	12-10	.210	#8		1.00	.37	.27	.81	
RC10-10F	50	12-10	.210	#10		1.00	.37	.27	.81	
RC1153	500	12-10	.210	#10		1.00	.37	.27	.81	
RC10-14F	50	12-10	.210	1/4"		1.12	.50	.27	.86	
RC1163	500	12-10	.210	1/4"		1.12	.50	.27	.86	
RC1124	1,000	12-10	.250	#8		1.10	.37	.27	.91	
RC1154	1,000	12-10	.250	#10		1.10	.37	.27	.91	

Nylon-Insulated Locking Fork



CAT. NO.	PKG. QTY.	WIRE RANGE	MAX. INS.	BOLT HOLE	REC. TOOL	DIMENSIONS				STOCK THICK.
						A	B	C	M	
RA18-6FL	100	22-16	.136	#6	ERG 2001	.86	.25	.25	.71	.02
RA2213	1,000	22-16	.136	#6		.86	.25	.25	.71	
RA18-8FL	100	22-16	.136	#8		.86	.29	.25	.71	
RA2243	1,000	22-16	.136	#8		.86	.29	.25	.71	
RA18-10FL	100	22-16	.136	#10		.86	.29	.25	.71	
RA2253	1,000	22-16	.136	#10		.86	.29	.25	.71	
RB14-6FL	100	18-14	.162	#6		.87	.25	.25	.71	.03
RB2213	1,000	18-14	.162	#6		.87	.25	.25	.71	
RB2214	1,000	18-14	.190	#6		.95	.25	.25	.79	
RB14-8FL	100	18-14	.162	#8		.87	.29	.25	.71	
RB2233	1,000	18-14	.162	#8		.87	.29	.25	.71	
RB14-10FL	100	18-14	.162	#10		.87	.29	.25	.71	
RB2253	1,000	18-14	.162	#10	ERG 2001	.87	.29	.25	.71	.04
RB2254	1,000	18-14	.190	#10		.95	.29	.25	.71	
RC10-6FL	50	12-10	.210	#6		.97	.31	.27	.81	
RC2203	500	12-10	.210	#6		.97	.31	.27	.81	
RC2204	1,000	12-10	.250	#6		1.07	.31	.27	.91	
RC10-8FL	50	12-10	.210	#8		1.00	.37	.27	.81	
RC2213	500	12-10	.210	#8		1.00	.37	.27	.81	
RC10-10FL	50	12-10	.210	#10		1.00	.37	.27	.81	
RC2223	500	12-10	.210	#10		1.00	.37	.27	.81	
RC2224	1,000	12-10	.250	#10		1.10	.37	.27	.91	
RC10-14FL	50	12-10	.210	1/4"		1.12	.50	.32	.86	
RC2233	500	12-10	.210	1/4"		1.12	.50	.32	.86	

Thomas & Betts

www.tnb.com

United States

Tel: 901.252.8000

800.816.7809

Fax: 901.252.1354

Canada

Tel: 450.347.5318


Fax: 450.347.1976

Technical Services

Tel: 888.862.3289


Vinyl-Insulated Fork Terminals

Vinyl-Insulation Fork — Expanded Insulation



CAT. NO.	PKG. QTY.	WIRE RANGE	MAX. INS.	BOLT HOLE	REC. TOOL	DIMENSIONS				STOCK THICK.
						A	B	C	M	
18RA-6FX	100	22-16	.170	#6	ERG 2001	.94	.25	.27	.81	.02
RA1167-170	1,000	22-16	.170	#6		.94	.25	.27	.81	
18RA-8FX	100	22-16	.170	#8		.97	.31	.27	.81	
RA1147-170	1,000	22-16	.170	#8		.97	.31	.27	.81	
18RA-10FX	100	22-16	.170	#10		.97	.31	.27	.81	
RA1157-170	1,000	22-16	.170	#10		.97	.31	.27	.81	
14RB-6FX	100	18-14	.200	#6		.97	.31	.27	.81	.03
RB647-200	1,000	18-14	.200	#6		.97	.31	.27	.81	
14RB-8FX	100	18-14	.200	#8		.97	.31	.27	.81	
RB657-200	1,000	18-14	.200	#8		.97	.31	.27	.81	
14RB-10FX	100	18-14	.200	#10		.97	.31	.27	.81	
RB1157-200	1,000	18-14	.200	#10		.97	.31	.27	.81	
10RC-8FX	50	12-10	.250	#8		1.11	.38	.27	.90	.04
RC1147-250	500	12-10	.250	#8		1.11	.38	.27	.90	
10RC-10FX	50	12-10	.250	#10		1.11	.38	.27	.90	
RC1157-250	500	12-10	.250	#10		1.11	.38	.27	.90	
10RC-14FX	50	12-10	.250	1/4"		1.17	.50	.37	.90	

Vinyl-Insulated Locking Fork



CAT. NO.	PKG. QTY.	WIRE RANGE	MAX. INS.	BOLT HOLE	REC. TOOL	DIMENSIONS				STOCK THICK.
						A	B	C	M	
18RA-6FL	100	22-16	.150	#6	ERG 2001	.97	.25	.25	.81	.02
RA2217	1,000	22-16	.150	#6		.97	.25	.25	.81	
RA2227	1,000	22-16	.155	#6		.97	.29	—	.81	
18RA-8FL	100	22-16	.150	#8		.97	.29	.25	.81	
RA2247	1,000	22-16	.150	#8		.97	.29	.25	.81	
18RA-10FL	100	22-16	.150	#10		.97	.29	.25	.81	
RA2257	1,000	22-16	.150	#10		.97	.29	.25	.81	
14RB-6FL	100	18-14	.170	#6		.97	.25	.27	.81	.03
RB2207	1,000	18-14	.170	#6		.97	.25	.27	.81	
RB2217	1,000	18-14	.170	#6		.97	.29	.27	.81	
14RB-8FL	100	18-14	.170	#8		.97	.29	.27	.81	
RB2237	1,000	18-14	.170	#8		.97	.29	.27	.81	
14RB-10FL	100	18-14	.170	#10		.97	.29	.27	.81	
RB2257	1,000	18-14	.170	#10		.97	.29	.27	.81	
10RC-6FL	50	12-10	.220	#6		1.09	.31	.27	.90	.04
RC2207	500	12-10	.220	#6		1.09	.31	.27	.90	
10RC-8FL	50	12-10	.220	#8		1.09	.37	.27	.90	
RC2217	500	12-10	.220	#8		1.09	.37	.27	.90	
10RC-10FL	50	12-10	.220	#10		1.09	.37	.27	.90	
RC2227	500	12-10	.220	#10		1.09	.37	.27	.90	
10RC-14FL	50	12-10	.220	1/4"		1.09	.49	.27	.90	
RC2237	500	12-10	.220	1/4"		1.09	.49	.27	.90	