

# DUAL BINDING POSTS


**01-1532-1-02XX BRIGHT TIN\*** } 10-32 THREADS

**01-1532-1-0300 GOLD PLATE**

**01-1504-1-02XX BRIGHT TIN\***

**01-1504-1-0300 GOLD PLATE** } 8-32 THREADS

FINISH COLOR



Post is completely insulated from chassis. Accommodates panels from 1/16" to 1/4" thick. Design of post allows for five ways to connect: accepts standard banana plug, clip on main shaft, up to No.14 wire thru cross hole clamped with head, wire looped around shaft and clamped with head, spade lug clamped with head. Insulation is molded lexan. Metal parts are brass.(electroplated).

\* Nut and inserts are nickel plated



1 RED HEAD + 1 BLK HEAD	RED	BLACK
00	12	10

## DUAL BINDING POST

### HEX HEAD

30 AMPERE CAPACITY

1000 WVDC MAX




**01-1533-1-02XX BRIGHT TIN\* 10-32 THREADS**

**01-1508-1-02XX GOLD PLATE 8-32 THREADS**

FINISH COLOR

30 AMPERE CAPACITY  
1000 WVDC MAX.





Post is completely insulated from chassis. Accommodates panels from 1/16" to 1/4" thick. Design of post allows for five ways to connect: accepts standard banana plug, clip on main shaft, up to No.14 wire thru cross hole clamped with head, wire looped around shaft and clamped with head, spade lug clamped with head. Insulation is molded lexan. Metal parts are brass.(electroplated)

Fluted caps. \* Nut and inserts are nickel plated

1 RED HEAD + 1 BLK HEAD	RED	BLACK
00	12	10

## DUAL BINDING POST

### FLUTED HEAD LIMITED OPENING




**01-1557-1-02XX BRIGHT TIN\* 6-32 THREADS**

**01-1557-1-0300 GOLD PLATE**

**01-1558-1-02XX BRIGHT TIN\* 8-32 THREADS**

FINISH COLOR



15 AMPERE CAPACITY  
1000 WVDC MAX.

Post is completely insulated from chassis. Accommodates panels from 1/16" to 1/4" thick. Design of post allows for five ways to connect: accepts standard banana plug, clip on main shaft, up to No.14 wire thru cross hole clamped with head, wire looped around shaft and clamped with head, spade lug clamped with head. Insulation is molded nylon.


Metal parts are brass.(electroplated)

\* Nut and inserts are nickel plated

1 RED HEAD + 1 BLK HEAD	RED	BLACK
00	12	10

**01-1590-1-0210 BRIGHT TIN\* 10-32 THREADS**

FINISH COLOR



30 AMPERE CAPACITY  
1000 WVDC MAX.

Post is completely insulated from chassis. Accommodates panels from 1/16" to 1/4" thick. Design of post allows for five ways to connect: accepts standard banana plug, clip on main shaft, up to No.14 wire thru cross hole clamped with head, wire looped around shaft and clamped with head, spade lug clamped with head. Insulation is molded lexan.



Metal parts are brass.(electroplated)

\* Nut and inserts are nickel plated

1 RED HEAD + 1 BLK HEAD	RED	BLACK
00	12	10


## DUAL BINDING POST

### MINIATURE FLUTED HEAD LIMITED OPENING



## 01-1111 SHORTING LINK FOR DUAL BINDING POST

Spring brass, nickel plated, 1/32" thickness. Designed for 3/4" centers. This shorting link is compatible with all of the above dual binding posts.



**CONCORD®**