





I.D.C SOCKET DUAL-ROW SR




MATERIALS:
INSULATOR:P.B.T.30%GLASS FIBER,UL94V-0
CONTACT MATERIAL:BRASS OR PHOSPHOR BRONZE,
GOLD FLASH OVER NICKEL

ELECTRICAL:
CURRENT RATING:1AMP.
INSULATION RESISTANCE:1000MΩ MIN.
DIELECTRIC WITHSTANDING:500VAC
OPERATING TEMPERATURE:-55°C~+105°C

AWP2-XX-7240-R

Number of Contacts
10/14/16/20/26/34/40/44/50



UNLESS OTHERWISE SPECIFIED TOLERANCE			
ANG.	±5°		
.0	±0.5	SCALE: AS SHOWN	
.00	±0.3	UNIT: mm	
.000	±0.2	DRAWN TERRY 10/07/05	
CHECKED Joe 10/07/05		DRAWN NAME: I.D.C. SOCKET DUAL-ROW	
APPROVED Mike 10/07/05		PITCH: 2.0mm	
DATE 10/07/05		PRODUCT NO. AWP2-XX-7240-R	
SIZE A4		FILE NAME:	
REV. A			

REV.	DESCRIPTION	DATE
A	ECN-0510053(Rita)	10/07/05