

- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click to remove) [Search Tips](#)

Text Search: 'TM2A-M39'

Your search criteria matched only one product, shown below



- Solid flat bottom surface provides maximum holding area
- For indoor use only
- Material: Nylon 6.6

Part Number	TM2A-M39
RoHS Compliancy Status	Compliant
Part Description	Cable Tie Mounts— User Supplied Adhesives
Product Type	Cable Tie Mounts- User Supplied Adhesive
Material	Heat Stabilized Nylon 6.6
Color	Natural
UL Recognized	E136577
Height (In.)	0.28
Height (mm)	7.0
Length (In.)	0.63
Length (mm)	16.0
Width (In.)	0.43
Width (mm)	10.8
CE Compliant	CT-ACC2 / 10.96
Environment	Indoor
Flammability Rating	V-2
Mounting Method	User Supplied Adhesive
Pricing Description	Cable Tie Mount, User App Adh., .43" (10.9mm)W
Sub Brand	Cable Tie Mount
Type	Tie Mount- User Supplied Adhesive
Used With Cable Ties	M, I, S
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.