




| LOC | DIST | P | F | REVISIONS |     |                           |  |         |      |
|-----|------|---|---|-----------|-----|---------------------------|--|---------|------|
|     |      |   |   | ZONE      | LTR | DESCRIPTION               |  | DATE    | APPD |
| GP  | 00   |   |   |           | K1  | REVISED PER ECO 05-008301 |  | 11MAY06 | JG   |



- 1 POLYESTER, BLACK, UL94 V-0.
- 2 CORING CONFIGURATION VARIES BY PART SIZE.
3. MAXIMUM ACCEPTABLE CABLE THICKNESS 0.97[.038].



|                  |                  |               |            |
|------------------|------------------|---------------|------------|
| 11.94<br>[.470]  | 15.14<br>[.596]  | 12            | 1-111614-7 |
| 7.98<br>[.314]   | 11.18<br>[.440]  | 8             | 1-111614-6 |
| 21.97<br>[.865]  | 25.17<br>[.991]  | 22            | 1-111614-5 |
| 67.97<br>[2.676] | 71.17<br>[2.802] | 68            | 1-111614-4 |
| 63.96<br>[2.518] | 67.18<br>[2.645] | 64            | 1-111614-3 |
| 59.97<br>[2.361] | 63.17<br>[2.487] | 60            | 1-111614-2 |
| 49.96<br>[1.967] | 53.16<br>[2.093] | 50            | 1-111614-1 |
| 43.97<br>[1.731] | 47.17<br>[1.857] | 44            | 1-111614-0 |
| 39.98<br>[1.574] | 43.18<br>[1.700] | 40            | 111614-9   |
| 33.96<br>[1.337] | 37.16<br>[1.463] | 34            | 111614-8   |
| 29.97<br>[1.180] | 33.17<br>[1.306] | 30            | 111614-7   |
| 25.96<br>[1.022] | 29.16<br>[1.148] | 26            | 111614-6   |
| 23.98<br>[.944]  | 27.18<br>[1.070] | 24            | 111614-5   |
| 19.96<br>[.786]  | 23.16<br>[.912]  | 20            | 111614-4   |
| 15.98<br>[.629]  | 19.18<br>[.755]  | 16            | 111614-3   |
| 13.97<br>[.550]  | 17.17<br>[.676]  | 14            | 111614-2   |
| 9.96<br>[.392]   | 13.16<br>[.518]  | 10            | 111614-1   |
| B                | A                | NO OF<br>POSN | PART NO    |

|                                                                                                                                 |                 |                   |
|---------------------------------------------------------------------------------------------------------------------------------|-----------------|-------------------|
| PART NO                                                                                                                         |                 |                   |
| DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES: ON: 2 PLC DEC ± 0.05 [.002] 3 PLC DEC ± - ANGLES ± - |                 |                   |
| DR 02-21-92 C.OBERMAN                                                                                                           |                 |                   |
| CHK 03-2-92 R.STONE                                                                                                             |                 |                   |
| APPD 03-2-92 R.LOCATI                                                                                                           |                 |                   |
| APPD 03-3-92 D.HOFFMAN                                                                                                          |                 |                   |
| PRODUCT SPEC 108-1372                                                                                                           |                 |                   |
| FINISH -                                                                                                                        |                 |                   |
| APPLICATION SPEC -                                                                                                              |                 |                   |
| WEIGHT -                                                                                                                        |                 |                   |
| NAME                                                                                                                            |                 |                   |
| STRAIN RELIEF, 2mm CL, AMP-LATCH                                                                                                |                 |                   |
| SIZE D                                                                                                                          | CAGE CODE 00779 | DRAWING NO 111614 |
| SCALE 10:1                                                                                                                      | SHEET 1 OF 1    |                   |