

RAD-CON-MCX-RPSMA-EX

Order No.: 2885621



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2885621>

Adapter cable for Ex zone 1, pigtail 90 cm MCX (m) -> RPSMA (m)

Commercial data

GTIN (EAN)	 4 046356 149495
Note	Made-to-order
sales group	H178
Pack	1 pcs.
Customs tariff	85442000
Catalog page information	Page 647 (IF-2009)

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Connection 1	Plug connector connection
Type of connection	Typ MCX (male)
Connection 2	Plug connector connection
Type of connection	Type RPSMA (male)
Fixed cable length	90 cm
Cable, attenuation	approx. 1.5 dB/m
Connection name	Plug connector connection
Type of connection	Typ MCX (male)

Ambient temperature (operation)	-40 °C ... 85 °C
ATEX	Ex II 2(1)G, EEx d mb [ia] IIC
UL, USA / Canada	Class I, Div. 1, 2, Groups A, B, C, D

Certificates / Approvals

Certification Ex: CUL-EX, UL-EX

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;