

Control Circuit Protection

Supplementary Protection, AC/DC Product Range

5SY5 70 mm mounting depth

Features

- Operating voltage to EN 60898 and EN 60947-2
 - 220 V DC/pole max.
 - 440 V AC max.
- Standards: EN 60 898-1, DIN VDE 0641 Part 11, IEC 60 898
- Additional components can be retrofitted.
- **Devices do not comply with UL1077**

Selection and ordering data

	I_n	MW ¹⁾	Characteristic B		Characteristic C		Weight 1 item kg
			Order No.	List Price \$ 1 item	Order No.	List Price \$ 1 item	
 1-pole 1 2	A						
	0.3	1	-		5SY5 114-7		0.147
	0.5		-		5SY5 105-7		
	1		-		5SY5 101-7		
	1.6		-		5SY5 115-7		
	2		5SY5 102-6		5SY5 102-7		
	3		-		5SY5 103-7		
	4		-		5SY5 104-7		
	6		5SY5 106-6		5SY5 106-7		
	8		-		5SY5 108-7		
	10		5SY5 110-6		5SY5 110-7		
	13		5SY5 113-6		5SY5 113-7		
	16		5SY5 116-6		5SY5 116-7		
	20		5SY5 120-6		5SY5 120-7		
	25		5SY5 125-6		5SY5 125-7		
	32 ¹⁾		5SY5 132-6		5SY5 132-7		
	40		5SY5 140-6		5SY5 140-7		
	50		5SY5 150-6		5SY5 150-7		
	63		5SY5 163-6		5SY5 163-7		
 2-pole 1 3 2 4	0.3	2	-		5SY5 214-7		0.304
	0.5		-		5SY5 205-7		
	1		-		5SY5 201-7		
	1.6		-		5SY5 215-7		
	2		-		5SY5 202-7		
	3		-		5SY5 203-7		
	4		-		5SY5 204-7		
	6		5SY5 206-6		5SY5 206-7		
	8		-		5SY5 208-7		
	10		5SY5 210-6		5SY5 210-7		
	13		5SY5 213-6		5SY5 213-7		
	16		5SY5 216-6		5SY5 216-7		
	20		5SY5 220-6		5SY5 220-7		
	25		5SY5 225-6		5SY5 225-7		
	32		5SY5 232-6		5SY5 232-7		
	40		5SY5 240-6		5SY5 240-7		
	50		5SY5 250-6		5SY5 250-7		
	63		5SY5 263-6		5SY5 263-7		

1) MW = modular width of 18 mm.
Depth = 70 mm.