









4 Pos.
(SCALE 4-1)




5~15 Pos.



NOTES:

1. MATERIAL: HOUSING - NYLON 66 (UL94V-0)
POST - TIN BRASS
2. APPLICABLE RECEPTACLE P/N 173977
3. THIS PART HAS BEEN OBSOLETE.



RECOMMENDABLE PCB LAYOUT
(PCB THK:0.8-1.6)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

10±0.2
30±0.5
100±1.0
ANGLE ±3°

tyco

Electronics

Shanghai, China

POST HEADER ASS'Y HORIZONTAL TYPE
(AMP CT CONNECTOR 2mm PITCH)

SIZE: 00779
QAGE CODE: 292253
DRAWING NO: 292253

Part No.	Black	Yellow	Blue	Natural	Pos.	A	B	C	D
7-292253-4	5	4	3	2	1	28	31.8	25.2	31.0
7-292253-5	5	4	3	2	1	26	29.8	23.2	29.0
7-292253-6	5	4	3	2	1	24	27.8	21.2	27.0
7-292253-7	5	4	3	2	1	22	25.8	19.2	25.0
7-292253-8	5	4	3	2	1	20	23.8	17.2	23.0
7-292253-9	5	4	3	2	1	18	21.8	15.2	21.0
7-292253-10	5	4	3	2	1	16	19.8	13.2	19.0
7-292253-11	5	4	3	2	1	14	17.8	11.2	17.0
7-292253-12	5	4	3	2	1	12	15.8	9.2	15.0
7-292253-13	5	4	3	2	1	10	13.8	7.2	13.0
7-292253-14	5	4	3	2	1	8	11.8	5.2	11.0
7-292253-15	5	4	3	2	1	6	9.8	3.2	9.0
7-292253-16	5	4	3	2	1	4	7.8	1.2	7.0
7-292253-17	5	4	3	2	1	2	5.8	0.2	5.0