

FLK 50/EZ-DR/FCN40/100/OMR-IN

Order No.: 2304160

The illustration shows the version FLK 50/EZ-DR/FCN40-OMR/OUT/...



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2304160>

System cable, with a 50-pos. flat-ribbon cable strip and a 40-pos. female connector, cable length: 1 m, for CJ1: ID231, ID261; CS1, C200H: ID111, ID216, ID217; CQM1: ID112, ID213, ID214

Commercial data

GTIN (EAN)	 4 017918 927363
Note	Made-to-order
sales group	I680
Pack	1 pcs.
Customs tariff	85444290
Catalog page information	Page 203 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
06/29/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A

Max. conductor resistance	0.16 Ω /m
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 50 °C
Number of positions, control side	40
Number of connectors, control side	1
Number of positions, module side	50
Number of connectors, modul side	1
Fixed cable length	1 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	10.5 mm
Shielding	no

Certificates / Approvals



Certification

CUL, UL

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;