

PART NAME	UTILIBOX (STYLE H)	PART NO.	CU-1476-MB
<u>MATERIAL</u> : ABS THERMOPLASTIC (FLAMMABILITY RATING OF 94-VO AT 0.070" THICKNESS AND CONTINUOUS USE TEMPERATURE OF 70° C)	LENGTH AND WIDTH DIMENSIONS ARE TAKEN FROM CLOSED END OF THE BOX. DIMENSIONS INCREASE SLIGHTLY AT OPEN END DUE TO TAPER.	FINISH: BODY - OUTSIDE SURFACES ARE TEXTURED FINISH WITH TEXTURED INSERT AREA. COVER - VERTICAL OUTSIDE SURFACES ARE TEXTURED. REMAINDER OF PART IS SMOOTH.	COLOR: BLACK
			NOTE: ALL DIMENSIONS HAVE $\pm 0.010$ TOLERANCE UNLESS OTHERWISE SPECIFIED.
			FOUR (4) #4 X 1/2 LG. SELF THREADING SCREWS WITH HOLLOW THREADS ARE SUPPLIED FOR MOUNTING COVER.

**FRONT VIEW (BODY)**

Dimensions: 2.598, 3.848, 1.750, 0.100, 0.090 DIA x 0.500 DEEP (4) HOLES, 0.180 DIA BOSS (4) PLACES.

**TOP VIEW (BODY)**

Dimensions: 2.598, 3.848, 0.100, 0.047 TYP., 0.187 POLISHED BAND, 0.100 TYP., 4.376, 2.723, 0.056.

**SIDE VIEW (BODY)**

Dimensions: 0.100, 0.067, 0.270, 2.003, 1.155, 0.808, 0.111 DIA, (AT TOP) (4) HOLES, 0.090 DIA x 0.250 DEEP (4) HOLES, 0.180 DIA BOSS (4) PLACES, 0.215 DIA, BOSS (4) PLACES, 0.090 DIA x 0.250 DEEP (4) HOLES, 0.111 DIA, (AT TOP) (4) HOLES, 0.056, 1.155, 0.808, 0.100, 0.047 TYP., 0.187 POLISHED BAND, 0.100 TYP., 4.376, 2.723, 0.056.

**FRONT VIEW (COVER)**

Dimensions: 5.500, 0.405, 0.120, 0.693, 0.405, 0.076, 0.100, 0.250, 3.250, 0.187 DIA (4) HOLES.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[CU-1476-MB](#)