

PART NAME	RACKMOUNT CHASSIS				PART No.	CH-14400 TO CH-14404 & CH-14410 TO CH-14414			
-----------	-------------------	--	--	--	----------	---	--	--	--

0.750 TYP.

0.328

0.250

0.156 DIA. (4) HOLES

0.278 x 0.406 DBLONG (4) HOLES

0.278 REF.

WHEN (F) IS 4.000

0.187 DIA. (4) HOLES

WHEN (F) IS 8.000

0.187 DIA. (6) HOLES

WHEN (F) IS 16.000

0.187 DIA. (8) PLACES

MATERIAL:
 CHASSIS _____ 0.050 THK. ALUMINUM
 PANEL _____ 0.120 THK. ALUMINUM

FINISH:
 ALL PARTS _____ NATURAL

PART NO.	A	B	C	D	E	F	G	H
CH-14400	19.000	1.750	1.250	1.437	17.000	4.000	4.120	0.719
CH-14401	19.000	1.750	1.250	1.437	17.000	8.000	8.120	0.719
CH-14402	19.000	1.750	1.250	1.437	17.000	16.000	16.120	0.719
CH-14403	19.000	3.500	3.000	3.187	17.000	8.000	8.120	1.594
CH-14404	19.000	3.500	3.000	3.187	17.000	16.000	16.120	1.594
CH-14410	24.000	1.750	1.250	1.437	22.000	4.000	4.120	0.719
CH-14411	24.000	1.750	1.250	1.437	22.000	8.000	8.120	0.719
CH-14412	24.000	1.750	1.250	1.437	22.000	16.000	16.120	0.719
CH-14413	24.000	3.500	3.000	3.187	22.000	8.000	8.120	1.594
CH-14414	24.000	3.500	3.000	3.187	22.000	16.000	16.120	1.594

PART NAME	CHASSIS COVER				PART No.	C-14430 TO C-14435 & C-14440 TO C-14445			
-----------	---------------	--	--	--	----------	---	--	--	--

MATERIAL: 0.050 THK. ALUMINUM

FINISH: NATURAL

(J) SPACES @ 0.500 = (K)

0.187 x 1.000 DBLONG (H) HOLES

0.156 DIA. (M) HOLES

(C) SPACES @ 1.250 = (D)

PART NO.	A	B	C	D	E	F	G	H	J	K	L	M
C-14430	17.000	4.000	1	1.250	1.375	7.500	-----	60	29	14.500	2.000	7
C-14431	17.000	8.000	4	5.000	1.500	7.500	3.000	150	29	14.500	-----	9
C-14432	17.000	16.000	10	12.500	1.750	7.500	7.000	330	29	14.500	-----	9
C-14433	22.000	8.000	4	5.000	1.500	10.000	3.000	200	39	19.500	-----	9
C-14434	22.000	16.000	10	12.500	1.750	10.000	7.000	440	39	19.500	-----	9
C-14435	22.000	4.000	1	1.250	1.375	10.000	-----	80	39	19.500	2.000	7
C-14440	17.000	4.000	-----	-----	-----	7.500	-----	-----	-----	-----	2.000	7
C-14441	17.000	8.000	-----	-----	-----	7.500	3.000	-----	-----	-----	-----	9
C-14442	17.000	16.000	-----	-----	-----	7.500	7.000	-----	-----	-----	-----	9
C-14443	22.000	8.000	-----	-----	-----	10.000	3.000	-----	-----	-----	-----	9
C-14444	22.000	16.000	-----	-----	-----	10.000	7.000	-----	-----	-----	-----	9
C-14445	22.000	4.000	-----	-----	-----	10.000	-----	-----	-----	-----	2.000	7