



Deutsche Version

[Home](#)
[About Us](#)

Products

Audio

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

☐ PRODUCTS
ONLY

Search

© Neutrik® AG
All rights reserved
[Legal Notices](#)

NEUTRIK




Audio

P Series

[back](#)

NC7FP-B-1



Product

Connector Type	XLR
Gender	female

Electrical

Capacitance between contacts	≤ 9 pF
Contact resistance	≤ 5 m Ω
Dielectric strength	1,5 kVdc
Insulation resistance	> 2 G Ω (initial)
Insulation resistance	> 1 G Ω (after damp heat test)
Rated current per contact	5 A
Rated voltage	50 V

Mechanical

Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wire size	max. 1,0 mm ²
Wire size	max. 18 AWG
Wiring	Solder contacts
Locking device	latch lock
Mounting direction	front
Chassis shape	P

Material

Contact plating	0,2 μ m Au hard alloy over 2 μ m Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Steel Ck67
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black chromium

Environmental

Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C