



Product Specification Data Sheet [Detachable Power Supply Cord]

PART NUMBER		REV	OVERALL RATING AND SPECIFICATIONS				ROHS COMPLIANT
9217-210		A	CURRENT	VOLTAGE AC	LENGTH		COLOR
Geographical Recognition ↓			2.5A	250V	1.85m	6'	Black
Brazil							
ELECTRICAL TESTING 100%		HI POT WIRE TO WIRE		CONTINUITY TEST		POLARITY TEST	SKIN HI POT
VISUAL INSPECTION 100%		3 kV FOR 2 SEC.		25A GND	20A L TO N	YES	6 kV LINE TO SKIN
PLUG TYPE:			BR/3				
DESIGN STANDARDS:			NBR 14136				
WIRE TERMINATIONS:			CRIMPED				
BLADES OR PINS:			BRASS, NICKEL PLATED				
DOUBLE INSULATED:			YES☒ NO☐				
OVER MOLDING:			PVC COMPOUND				
COLOR:			BLACK				
3 WIRE CORDAGE TYPE:			H05VVF3G0.75mm ²				
SPECIALS:			NONE				
FLAMMABILITY / TEMP:			94HB / 70 ^o C				
DIELECTRIC :			2000V				
JACKET INSULATION:			PVC, O.D. 6.60mm+/-0.20				
COLOR:			BLACK				
CONDUCTORS:			23 x 0.197mm				
WIRE INSULATION:			PVC, O.D. 2.30mm				
COLORS G, L, N:			YE/GN, BN, BU				
CONNECTOR TYPE:			C5				
DESIGN STANDARDS:			EN60320/C5				
WIRE TERMINATIONS:			CRIMPED				
CONTACT SLEEVES:			PHOSPHOR BRONZE				
DOUBLE INSULATED:			YES☒ NO☐				
OVER MOLDING:			PVC COMPOUND				
COLOR:			BLACK				

Component Approvals:







MARKINGS:
***JF* <OVE> <HAR> H05V
VF3G0,75MM2*1095*CE**

COMPONENT APPROVALS
<HAR> CE


Component Approvals:



CE



Dimensions in mm unless noted



Issued Date: 10/2/2009

Rev Date: 10-19-2009, correct length 6' 1.85m

Issued By: R. Linville

Rod Linville

Approved By: G. Kysely

Gregor Kysely

FELLER POWER CORDS

9100 Industrial Blvd., Leland, NC 28451
PROPRIETARY DATA

PH: (910) 383-6920 FX: (910) 383-6921 e-mail: sales@feller-us.com
www.feller-us.net SPECIFICATIONS SUBJECT TO CHANGE