





Identification	Part No.	Drawing	Dimensions in mm
Fibre optic cable, double ended, multi mode, 62.5 µm Length: a = 1 m a = 5 m a = 10 m a = 20 m a = 40 m a = 50 m a = 100 m	33 58 211 0010 001 33 58 211 0050 001 33 58 211 0100 001 33 58 211 0200 001 33 58 211 0400 001 33 58 211 0500 001 33 58 211 1000 001	double ended  a = length	
Fibre optic cable, single ended, multi mode, 62.5 µm Length: a = 1 m a = 5 m a = 10 m a = 20 m a = 40 m a = 50 m a = 100 m	33 58 111 0010 001 33 58 111 0050 001 33 58 111 0100 001 33 58 111 0200 001 33 58 111 0400 001 33 58 111 0500 001 33 58 111 1000 001	single ended  a = length	Protection level: IP 65 / IP 67
Fibre optic breakout cable, multi mode, 62.5 µm Length: 10 m Length: 20 m Length: 100 m	33 58 751 0100 001 33 58 751 0200 001 33 58 751 1000 001		PUR jacket 2-fibre multi mode 62.5 µm Outer diameter: 7 mm Min. bending radius: Installation: 10.5 cm Operating: 7.0 cm