


PART NAME	NEMA 4X DIE CAST ALUMINUM ENCLOSURE	PART No.	AN-1305, AN-1305-G, AN-2805 & AN-2805-B	REV. DATE	12-17-08
-----------	-------------------------------------	----------	---	-----------	----------

MATERIAL: ALUMINUM ALLOY #ADC-12




FINISH: NATURAL (NO SUFFIX)
GRAY (SUFFIX -G)
SMOOTH BLACK (SUFFIX -B)

NOTES:


- 1) FOUR (4) M4 x 20mm (0.787") LG. SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE ± 0.005 TOLERANCE
ALL OTHER DIMENSIONS HAVE ± 0.015 TOLERANCE




SECTION "C-C"
* DIMENSIONS ARE AT
BOTTOM OF ENCLOSURE





BODY



SECTION "A-A"



COVER



PART NO. AN-2805 & AN-2805-B
ARE SUPPLIED WITH A WELDED
ON MOUNTING BRACKET ONLY.