

T120S0PPH4

Heavy Duty Cable Tie, 8.9" Long, 120lb Tensile Strength, PP, Black, 500/pkg

Article Number: 111-12827

Part Number: T120S0PPH4

Type: T120S

➔ Find a Distributor

→ Order Samples

➔Get Technical Drawings



➔ **Base Data**

Part No.	T120S0PPH4
Type	T120S
Color	Black (BK)
Features	• Polypropylene cable ties provide excellent resistance to chemicals and salts. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

➔ Product Dimensions

Min. Tensile Strength	60.0lbs / 267.0N
Length (L)	8.9" / 225.0mm
Width (W) (imperial)	0.3"
Width (W)	7.6mm
Min. Ø Bundle	0.2" / 5.0mm
Max. Ø Bundle	2.2" / 55.0mm
Thickness	1.6mm

➔ Material and Specifications

Material	Polypropylene (PP)
Flammability	UL94 HB
Material Specification	RoHS / HF
Operating Temperature	-40 °F to +239 °F (-40 °C to +115 °C)
ROHS Conformity	
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

 Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	500
Carton Qty.	1000
EAN code	4031026312026
UPC	089306061700

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)

[Home](#) | [About HellermannTyton](#) | [Products](#) | [Careers](#) | [Contact](#) | [Terms](#)

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512