



Rotary Switches


10YQ018, 10YQ025

10YQ026, 10YQ034

10YQ043, 10YQ062

10YQ110, 10YQ112

Dimensions: mm (in)



☒ STOPPER
P.C.B MOUNTING HOLE

Electrical Specifications:

- Rating: 0.3A/125VAC
- Contact resistance: 50m Ω max.
- Insulation resistance: 100M Ω @ 500VDC min.
- Dielectric strength: 250VAC for 1 minute

Mechanical Specifications:

- Type: PC mount; non-shorting contact (break before make)
- Rotation torque: 1.0+0.5KG/cm

Materials:

- Hardware included: 1 hexagon nut & 2 washers
- Shaft: 3/8"

Mouser Stock No.	Poles	Position
10YQ018	1	8
10YQ025	2	5
10YQ026	2	6
10YQ034	3	4
10YQ043	4	3
10YQ062	6	2
10YQ110	1	10
10YQ112	1	12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha \(Taiwan\):](#)

[SR2512-0206-19R0B-E9-N-W](#) [SR2512-0403-19R0B-E9-N-W](#) [SR2512-0110-19R0B-E9-N-W](#) [SR2512-0112-19R0B-E9-N-W](#) [SR2512-0304-19R0B-E9-N-W](#) [SR 2512-0108-19R0B-E9-N-W](#) [SR2512-0602-19R0B-E9-N-W](#)